


www.functionaldevices.com

## UNINTERRUPTIBLE POWER SUPPLY KIT

# PSH600-UPS

Kit Consisting of Enclosed Power Control Center Model PSH2RB10 (10 Amp Switch / Circuit Breaker, Two (2) 120 Vac Outlets, Terminals, 120 Vac Input) with a 600 VA UPS. (No Status Contacts)



# Shown Without Cover



# SPECIFICATIONS

#### UPS

UPS: 600VA Backup Time: 2.5 Min. @ Full 600 VA Load 10 Min. @ 1/2 Load Power Consumption Up to 3 Amp @120 Vac Max Load: 330 Watt Frequency: 50/60 Hz Temperature Rating of UPS: 32 to 104° F UPS Transfer Time: 6ms Approvals: UL Listed, UL1778

## PSH2RB10

Operating Temperature: -30 to 140° F Humidity Range: 5 to 95% (noncondensing) Main Breaker ON/OFF: Switch / Breaker (10 Amp) Approvals: UL Listed, UL916, C-UL, CE, ROHS Dimensions: 12.000" x 14.000" x 6.000" Metal Housing with Screw Cover

#### Notes:

- To order without UPS, so that any other commercial UPS with appropriate ratings and within housing space limitations may be used, see model PSH2RB10.
- To order interface board for replacement or for separate use,
- order model PSMN2RB10. • Average battery life: 3-5 years
- depending on the number of discharge cycles and environmental temperature
- UPS may change based on quality and availability

