



DC POWER SUPPLY: 120 VAC TO 24 VDC

PSMN40A24DS

2.75" Track Mount Isolated Linear DC Power Supply, 120 Vac to 24 Vdc, 1 Amp



SPECIFICATIONS

Voltage Input: 120 Vac
Voltage Output: 24 Vdc Isolated
Frequency: 50/60 Hz
Overload Protection: Electrical and Thermal, Auto-Reset
Operating Temperature: -30 to 140° F
Humidity Range: 5 to 95% (noncondensing)
Power Status: LED On = Activated
Dimensions: 2.500" x 2.750" x 5.000" (without track)
 2.800" x 2.750" x 5.000" (in track)
Track Mount: 2.750"
 MT212-6 Mounting Track Supplied
ON/OFF Switch: 2 Position
Approvals: UL916, C-UL, CE, RoHS

Output Current Ratings:
 1 A @ 24 Vdc

Input Current Rating:
 400 mA Maximum

Percent Ripple:
 0.0016%, 24 Vdc @ 1 A

Regulation:
 Load: 0.50% No Load to Full Load
 Line: 25.0000 mV/V