

(800) 888-5538


🔀 sales@functionaldevices.com

www.functionaldevices.com

## **15 AMP TRACK MOUNT CONTROL RELAY**

#### **RIBM24S**

4.00<sup>"</sup> Track Mount Relay 15 Amp SPST + Override with 24 Vac/dc Coil



# CCC ROHS



#### **SPECIFICATIONS**

 # Relays & Contact Type: One (1) SPST Continuous Duty Coil Expected Relay Life: 10 million cycles minimum mechanical
Operating Temperature: -30 to 140° F
Humidity Range: 5 to 95% (noncondensing)
Operate Time: 6ms
Relay Status: LED On = Activated

Dimensions: 1.250" x 4.000" x 1.750" Track Mount: 4.000"

#### MT4 Mounting Track Sold Separately

Approvals: UL Listed, UL916, UL864, C-UL California State Fire Marshal, CE, RoHS Gold Flash: No Override Switch: Yes

### Contact Ratings:

15 Amp General Use @ 125 Vac 10 Amp General Use @ 277 Vac 10 Amp Resistive @ 30 Vdc (N/O) 7 Amp Resistive @ 30 Vdc (N/C) 1/2 HP @ 125 Vac 1 HP @ 250 Vac 1/4 HP @ 277 Vac C300 Pilot Duty

#### Coil Current:

26 mA @ 20 Vac 31 mA @ 24 Vac 48 mA @ 35 Vac 14 mA @ 20 Vdc 18 mA @ 24 Vdc 28 mA @ 35 Vdc

#### Notes:

 Must cut appropriate jumper to select Normally Open or Normally Closed

Coil Voltage Input:

24 Vac/dc ; 50-60 Hz Drop Out = 3 Vac / 3.8 Vdc

Pull In = 20 Vac / 20 Vdc