


30 AMP TRACK MOUNT CONTROL RELAY

RIBM24ZL

4.00" Track Mount Relay 30 Amp DPST-N/O with 24 Vac/dc Coil













SPECIFICATIONS

Relays & Contact Type: One (1) DPST Continuous Duty Coil Expected Relay Life: 10 million cycles minimum mechanical

Operating Temperature: $-30 \text{ to } 140^{\circ} \text{ F}$

Humidity Range: 5 to 95% (noncondensing)

Operate Time: 18ms

Relay Status: LED On = Activated **Dimensions:** 2.350" x 4.000" x 2.750"

Track Mount: 4.000"

MT4 Mounting Track Sold Separately

Approvals: UL Listed, UL916, UL864, C-UL California State Fire Marshal, CE, RoHS

Gold Flash: Yes Override Switch: No

Contact Ratings:

30 Amp Resistive @ 300 Vac 25 Amp Resistive @ 28 Vdc 15 Amp Resistive @ 600 Vac 20 Amp Ballast @ 277-480 Vac Not rated for Electronic Ballast 3 HP @ 480-600 Vac 2 HP @ 240/277 Vac 1 HP @ 120 Vac 770 VA Pilot Duty @ 120 Vac 1158 VA Pilot Duty @ 240 Vac 1109 VA Pilot Duty @ 277 Vac 1640 VA Pilot Duty @ 480 Vac

Heavy Pilot Duty @ 600 Vac

Coil Current:

110 mA @ 20 Vac 138 mA @ 24 Vac 55 mA @ 20 Vdc 55 mA @ 24 Vdc 77 mA @ 30 Vdc

Coil Voltage Input:

24 Vac/dc; 50-60 Hz Drop Out = 2.1 Vac / 3.8 Vdc Pull In = 18 Vac / 22 Vdc

• Order Normally Closed by adding "-NC" to end of model number