

# Roof Flashings - Aluminum



## DESCRIPTION

**Black Swan's Aluminum Roof Flashings** provides weather sealings for pipes and vents protruding through roofs. **Aluminum Roof Flashings** are deep drawn 24 gauge aluminum base with EPDM rubber collar permanently attached. Fits up to a 40° roof pitch. Not for hot mop applications. Base meets Specifications ASMS4006, ASTM B-209, Fed QQA-250/2, UNS A 93003. EPDM rubber collar injection molded to offer superior resistance to weather, ozone and oxidation. EPDM durometer hardness Shore A60 meets AMS 67206, ASTM BA615.

**Note: Do not use petroleum based products on collar.**

---

## UPC NUMBER AND CARTON INFORMATION

STOCK NO.	SIZE	UPC NUMBER	CARTON CUBIC FEET
16100	1.25" x 1.50"	0 54647 16100 6	.677
16110	2"	0 54647 16110 5	.677
16120	3"	0 54647 16120 4	.859
16130	4"	0 54647 16130 3	1.11