

Roof Flashings - Thermoplastic



DESCRIPTION

Black Swan Thermoplastic Roof Flashing provides weather sealings for pipes and vents protruding through roofs. Black Swan's **Thermoplastic Roof Flashing** is an injection molded polypropylene base with 14 melt flow and 11 notched Izod for superior impact resistance. Thermoplastic base meets ASTM D1238, 120D, D56 Gardner impact D3029 Flex Modulus 115,000 psi, Tensile 2800 psi, TPR collar molded onto base to form one-piece permanent bonding of materials. Fits roofs up to 45° pitch. Not for hot mop applications. Collar durometer hardness Shore A60 meets ASTM D 2240. Tensile at break 900 psi. ASTM D412 and 670% elongation.

Note: Do not use petroleum based products on collar.

UPC NUMBER AND CARTON INFORMATION

STOCK NO.	SIZE	UPC NUMBER	CARTON CUBIC FEET
16300	1.25" x 1.50"	0 54647 16300 0	.486
16310	2"	0 54647 16310 9	.486
16320	3"	0 54647 16320 8	.777
16330	4"	0 54647 16330 7	.777