






SIB02S

Enclosed Switch 20 Amp, 3 Position Maintained, On/Off/On









SPECIFICATIONS

Operating Temperature: -30 to 140° F

Humidity Range: 5 to 95% (noncondensing) **Dimensions:** 1.700" x 2.800" x 1.500" (w/.500" NPT Nipple) Wires: 16", 600V Rated

Approvals: UL Listed, UL916, C-UL, CE, RoHS Housing Rating: UL Accepted for Use in Plenum, NEMA 1

Switch Ratings:

20 Amp Resistive @ 277 Vac 1110 VA Pilot Duty @ 277 Vac 770 VA Pilot Duty @ 120 Vac 20 Amp Ballast @ 277 Vac 10 Amp Tungsten @ 120 Vac

2 HP @ 277 Vac 1 HP @ 120 Vac

Notes:

• Switch position label can be custom printed according to your needs, simply consult factory