

Hand Tools



TT-221 ClikGrip 10" Auto Adjusting Plier

- Simple, quick adjusting design (no button to press or channels to lock)
- Hi-strength Chrome Vanadium Steel with non-reflective black oxide finish
- Only one hand needed to adjust size with a light squeeze of the handles
- Jaws stay parallel and grip flat, round, or irregular shaped objects
- Jaws maintain spacing when pressure is released (less hand fatigue)
- Cushioned, non-slip handles



TT-240 PowrStrip Automatic Wire Stripper

- Automatically strips wire from 8 to 30 AWG
- Easily crimps insulated and non-insulated wire
- Built-in wire cutter
- Comfortable and lockable ErgoTex spring loaded handles
- Ideal for low voltage and alarm installations



TT-242 CablCut Cable Cutter

- Cuts multi-wire copper cable up to 3/8" diameter
- Curved double ground SK-5 cutting blades
- Precision 10 to 20 AWG wire stripper
- Comfortable and lockable ErgoTex handles
- Corrosion resistant Black Oxide finish



TT-260 CrossJaw 13" Long Needle Nose Plier

- Serrated jaws can easily grip small objects
- 13" extended reach and narrow profile allow access to hard to reach areas
- Twin X joint allows access with minimal handle movement
- Corrosion resistant
- Flat rivet design
- Rubberized Grips



TT-270 8" Lineman Plier

- Clean cut from soft wire to high tensile wire
- Hot forged Chromium molybdenum steel
- Precise & ultra-smooth joint with no side play
- Serrated jaws
- Capacity: Medium hard wire – 0.15" (3.8 mm)/ Hard Wire – 0.1" (2.5 mm)
- PVC dipped handle



TT-275 8" Long Nose Plier

- Serrated jaws for easy gripping
- Hot forged Chromium molybdenum steel
- Precise & ultra-smooth joint with no side play
- Capacity: Medium hard wire – 1.3" (3.2 mm)/ Hard Wire – 0.1" (2.2 mm)
- PVC dipped handle



TT-280 10" Water Pump Plier

- 19 smooth position adjustments
- Induction hardened jaws up to 58HRC. for high wear resistance
- Jaw capacity: 1.9" (50mm)
- Grip tie by squeezing lower jaw handle for one hand wrenching
- Pinch proof design
- PVC dipped handle



TT-285 10" Crimping Plier

- For insulated and non-insulated terminals
- Copper wire cutter up to 12AWG (2mm)
- Material: Drop forged, heat treated middle carbon steel
- Drop forged 22-10 AWG
- PVC dipped handle



TT-290 6-in-1 Multifunctional Pliers

- Polished, Chrome Vanadium material
- Drop Forged & Heat Treated for exceptional strength & durability
- 6 in 1 Functions
 1. Gripping and Looping
 2. Screw Extractor
 3. Stripping 10-18 AWG Solid 12-20 AWG stranded
 4. Wire Cutting 2.0mm
 5. Screw Shearing: 6-32 & 8-32 screw
 6. Crimping
- Thermoplastic Rubber handle



TT-300 Punchdown Tool

- Easily terminate and cut CAT 3/5e/6 cables
- Built-in Hook and Spudger Tool
- Twist and lock blade
- Internal blade storage compartment
- Torque capability



TT-320 8-Piece Quick Change Ratchet Crimper

- 7 interchangeable die heads for the most commonly used insulated and non-insulated terminals
- 4140 forged steel die heads with zinc phosphate surface treatment
- Carbon Steel Crimper Body
- Polypropylene (PP) and Thermoplastic Rubber (TPR) Handles

