

HOM115PCAFI

Mini circuit breaker, Homeline, 15A, 1 pole, 120 VAC, 10 kA AIR, combo arc fault, plug on neutral, plug in mount



Main

Product	Miniature circuit-breaker
Range	Homeline
Current Rating	15 A
Certifications	UL Listed
Voltage Rating	120 V AC
Mounting Type	Plug-in
Number of Poles	1P
Short Circuit Current Rating	10 kA
Number of Spaces	1
Circuit Breaker Type	Combination ARC-fault
Ratings	HACR rated
Electrical Connection	Screw clamp terminals
Wire Size	AWG 14...AWG 8 aluminium/copper)1 AWG 14...AWG 10 copper)2

Complementary

Connections - terminals	Plug-on neutral
Tightening torque	35.40 lbf.in (4.0 N.m) 0.00...0.01 in ² (2.5...6 mm ²) (AWG 14...AWG 8)
Height	3.13 in (79.50 mm)
Width	1 in (25.40 mm)
Depth	2.98 in (75.69 mm)

Environment

Ambient air temperature for operation	104 °F (40 °C)
---------------------------------------	----------------

Ordering and shipping details

Category	06301 - HOM SINGLE POLE ARC FAULT CIRCUIT BREAKER
Discount Schedule	DE3D
GTIN	00785901950806
Nbr. of units in pkg.	1
Package weight(Lbs)	0.65 lb(US) (0.29 kg)
Returnability	Yes
Country of origin	MX

Packing Units

Unit Type of Package 1	PCE
Package 1 Height	4.00 in (10.16 cm)
Package 1 width	1.40 in (3.556 cm)
Package 1 Length	5.10 in (12.954 cm)
Unit Type of Package 2	CAR
Number of Units in Package 2	40
Package 2 Weight	24.45 lb(US) (11.09 kg)
Package 2 Height	4.30 in (10.922 cm)
Package 2 width	13.70 in (34.798 cm)

Package 2 Length	20.90 in (53.086 cm)
Unit Type of Package 3	PAL
Number of Units in Package 3	2400
Package 3 Weight	1494.00 lb(US) (677.666 kg)
Package 3 Height	44.50 in (113.03 cm)
Package 3 width	42.00 in (106.68 cm)
Package 3 Length	42.00 in (106.68 cm)

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
EU RoHS Directive	Compliant EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End Of Life Information
Halogen content performance	Halogen free product

Contractual warranty

Warranty	Lifetime
----------	----------