



Main

Range	9080FB
Product	Fuse holder

Complementary

Current Rating	30 A
[Ue] rated operational voltage	<= 250 V AC/DC
Fuse type	H
Fuse size	0.5625 x 2 in
Number of poles	3
Electrical connection	Pressure wire clamp
Wire Gauge	AWG 14...AWG 10 copper or aluminium
SCCR	10 kA UL 512
Product certifications	CE CSA file 70360 class 6225 01 UL listed file E40747 CCN IZLT
Operating Temperature	-40...257 °F (-40...125 °C)
Mounting Type	Surface mount
Block Material	Thermoplastic block
Wire stripping length	0.4375 in (11.11 mm)
Terminal Tightening Torque	Screw terminals 25 lbf.in (2.82 N.m) AWG 14...AWG 10 copper
Height	3 in (76.20 mm)
Width	2.95 in (74.93 mm)
Depth	1.38 in (35.05 mm)

Ordering and shipping details

Category	21701 - 9080 FB
Discount Schedule	CP1
GTIN	00785901097075
Nbr. of units in pkg.	1
Package weight(Lbs)	1 lb(US) (0.45 kg)
Returnability	Yes
Country of origin	US

Packing Units

Unit Type of Package 1	PCE
Package 1 Height	1.40 in (3.556 cm)
Package 1 width	3.00 in (7.62 cm)
Package 1 Length	3.20 in (8.128 cm)
Unit Type of Package 2	CAR

Number of Units in Package 2	20
Package 2 Weight	5.13 lb(US) (2.327 kg)
Package 2 Height	4.00 in (10.16 cm)
Package 2 width	7.60 in (19.304 cm)
Package 2 Length	13.00 in (33.02 cm)

Offer Sustainability

California proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov
REACH free of SVHC	Yes
EU RoHS Directive	Compliant EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration

Contractual warranty

Warranty	18 months
----------	-----------