

# Product data sheet

## Characteristics

# 9422RM1

Disconnect mechanism, circuit breaker, variable depth, 800/1200A, 3 pole, operator only, for PowerPact M and P breakers



### Main

Range	9422R
Product	Circuit Breaker Mechanism
Mounting Type	Flange rod variable depth
Certifications	CSA UL Recognized
Circuit Breaker Type	PowerPact M or P 3
Handle Type	Ordered separately

### Ordering and shipping details

Category	21732 - 9422
Discount Schedule	CP1
GTIN	00785901958673
Nbr. of units in pkg.	1
Package weight(Lbs)	14 lb(US) (6.35 kg)
Returnability	Yes
Country of origin	MX

### Packing Units

Package 1 Height	9.00 in (22.860 cm)
Package 1 width	14.70 in (37.338 cm)
Package 1 Length	26.30 in (66.802 cm)

### Offer Sustainability

California proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to <a href="http://www.P65Warnings.ca.gov">www.P65Warnings.ca.gov</a>
EU RoHS Directive	Compliant <a href="#">EU RoHS Declaration</a>
Mercury free	Yes
RoHS exemption information	<a href="#">Yes</a>
China RoHS Regulation	<a href="#">China RoHS Declaration</a>
PVC free	Yes

### Contractual warranty

Warranty	18 months
----------	-----------

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.