



### Main

Range of product	Harmony 9001K
Product or component type	Mushroom head push-button
Device short name	K
Type of operator	Spring return
Operator profile	Green mushroom Ø 35 mm
Operator additional information	Screw-in with set screw security

### Complementary

Bezel material	Chromium plated metal
Mounting diameter	1.18 in (30 mm)
Light source	without
Light source	Without
Light block supply	Without supply
Contacts type and composition	1 C/O
Connections - terminals	Screw clamp terminals
Operating position	Any position
[Ie] rated operational current	10 A, AC-15 10 A, DC-13
Contact operation	Standard
Device presentation	Complete product

### Environment

Product certifications	NEMA CE UL listed file E42259 CCN NKCR CSA LR 25490 class 3211 03
NEMA degree of protection	NEMA 1/2/3/3R/4/6/12/13

### Ordering and shipping details

Category	21426 - 9001 K (NOT KA,KM,KX)
Discount Schedule	CS1
GTIN	00785901033479
Nbr. of units in pkg.	1
Package weight(Lbs)	0.5 lb(US) (0.23 kg)
Returnability	No
Country of origin	MX

### Packing Units

Package 1 Height	11.43 in (29.032 cm)
Package 1 width	4.50 in (11.430 cm)
Package 1 Length	29.03 in (73.742 cm)

## Offer Sustainability

Sustainable offer status	Green Premium product
California proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to <a href="http://www.P65Warnings.ca.gov">www.P65Warnings.ca.gov</a>
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) <a href="#">EU RoHS Declaration</a>
Mercury free	Yes
RoHS exemption information	<a href="#">Yes</a>
China RoHS Regulation	<a href="#">China RoHS Declaration</a>
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.

## Contractual warranty

Warranty	18 months
----------	-----------