



Main

| | |
|---------|-------------------------|
| Product | Surge protection device |
| Range | Surgelogic |

Complementary

| | |
|---------------------------|-----------------------------|
| Surge Current | 40 kA |
| Voltage Rating | 480Y/277 V AC |
| Number of Phases | 3 phase |
| Wiring Configuration | 4-wire |
| Connection | Wire AWG 12 copper |
| MCOV | 180 V |
| Nominal Discharge Current | 10 kA |
| SCCR | 200 kA |
| Local Signalling | Status LED normal operation |
| Mounting Support | Panel mounting |
| Height | 3.07 in (78 mm) |
| Width | 3.62 in (92 mm) |
| Depth | 2.64 in (67 mm) |
| Cable length | 24 in (609.60 mm) |

Environment

| | |
|--------------------|--------------------------------------|
| Enclosure Rating | NEMA 4X |
| Enclosure Material | Black Plastic |
| Standards | UL 1449:ed. 4 CSA C22.2 No 8:1986 |
| Ambient Operating | 149 °F (65 °C) |

Ordering and shipping details

| | |
|-----------------------|-------------------------------|
| Category | 08462 - SURGE PROTECTION SDSA |
| Discount Schedule | DE1B |
| GTIN | 00785901558200 |
| Nbr. of units in pkg. | 1 |
| Package weight(Lbs) | 1 lb(US) (0.45 kg) |
| Returnability | Yes |
| Country of origin | MX |

Packing Units

| | |
|------------------|---------------------|
| Package 1 Height | 3.40 in (8.636 cm) |
| Package 1 width | 4.00 in (10.160 cm) |
| Package 1 Length | 5.00 in (12.700 cm) |

Offer Sustainability

| | |
|----------------------------|--|
| California proposition 65 | WARNING: This product can expose you to chemicals including: DINP, which is known to the State of California to cause cancer, and DIDP, which is known to the State of California to cause birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov |
| REACH Regulation | REACH Declaration |
| EU RoHS Directive | Compliant EU RoHS Declaration |
| Mercury free | Yes |
| RoHS exemption information | Yes |
| China RoHS Regulation | China RoHS Declaration |

Approximate Dimensions

