



## Main

Range	Acti 9
Product or component type	Comb busbar
Accessory / separate part category	Connection accessory
Lines description	3L + N
Length in 18 mm modules	57

## Complementary

Number of ways	14 ways N + 3 L
Poles configuration for 1 way	1 x 3P + N 1 x 4P
Connection pitch	0.71 in (18 mm)
Connector type	Tooth
Distance between way	2.83 in (72 mm)
Marking	N L1 L2 L3
Insulation	Insulated
Device presentation	Cuttable
Provided equipment	Set of 10 end piece
[Ie] rated operational current	100 A 104 °F (40 °C)
[Ue] rated operational voltage	415 V AC
[Ui] rated insulation voltage	500 V AC IEC 61439-2
Mounting mode	Horizontal
Mounting location	Top or bottom tunnel type terminals Top or bottom on double terminal
9 mm pitches	114
Width	39.37 in (1000 mm)
Color	White (RAL 9003)
Range compatibility	Acti 9 iC60 Acti 9 iK60 Acti 9 iID Acti 9 iID K Acti 9 iSW Acti 9 iSW-NA Multi 9 C60

## Environment

Standards	IEC 60947-7-1 IEC 61439-2
Fire resistance	1760 °F (960 °C) 30 s ) IEC 60695-2-1
Pollution degree	3 conforming to IEC 60947-7-1
IP degree of protection	IP20 with end-pieces and tooth covers

## Ordering and shipping details

Category	01078 - DE2 MISC
Discount Schedule	DE2
GTIN	03606480485176
Nbr. of units in pkg.	5
Package weight(Lbs)	1.61 lb(US) (0.73 kg)
Returnability	No
Country of origin	DE

## Packing Units

Unit Type of Package 1	PCE
Package 1 Height	1.10 in (2.8 cm)
Package 1 width	39.37 in (100 cm)
Package 1 Length	0.79 in (2 cm)
Unit Type of Package 2	CAR
Number of Units in Package 2	5
Package 2 Weight	8.63 lb(US) (3.916 kg)
Package 2 Height	2.28 in (5.8 cm)
Package 2 width	3.54 in (9 cm)
Package 2 Length	41.14 in (104.5 cm)
Unit Type of Package 3	P12
Number of Units in Package 3	270
Package 3 Weight	492.65 lb(US) (223.464 kg)
Package 3 Height	44.09 in (112 cm)
Package 3 width	47.24 in (120 cm)
Package 3 Length	31.50 in (80 cm)

## Offer Sustainability

Sustainable offer status	Green Premium product
REACH free of SVHC	Yes
EU RoHS Directive	Compliant <a href="#">EU RoHS Declaration</a>
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	<a href="#">Yes</a>
China RoHS Regulation	<a href="#">China RoHS Declaration</a>
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.

## Contractual warranty

Warranty	18 months
----------	-----------