



Main

Product or component type	Single Throw Safety Switch
Series name	General duty

Complementary

Device composition	Neutral (factory installed)
Disconnect device type	Fusible disconnect
Short-circuit current	100 kA maximum cartridge
Device mounting	Surface
Number of poles	2
Electrical connection	Lugs
[Ue] rated operational voltage	120/240 V AC
Maximum Horse Power Rating	15 Hp 240 V at AC 50-60 Hz for 1 phase conforming to NEC 240.6 25 Hp 240 V at AC 50-60 Hz for 3 phase conforming to NEC 240.6 60 hp 240 V at AC 50-60 Hz for 3 phase conforming to NEC 430.52
AWG gauge	AWG 6...250 kcmil copper or aluminium
Tightening torque	275 lbf.in (31.07 N.m) (AWG 6...250 kcmil)
Height	29.25 in (742.95 mm)
Width	19 in (482.60 mm)
Depth	8.5 in (215.90 mm)

Environment

Product certifications	CSA
NEMA degree of protection	NEMA 3R galvanized steel

Ordering and shipping details

Category	00106 - D & DU SW,NEMA3R, 30-200A
Discount Schedule	DE1A
GTIN	00785901391562
Nbr. of units in pkg.	1
Package weight(Lbs)	43.13 lb(US) (19.56 kg)
Returnability	Yes
Country of origin	US

Packing Units

Package 1 Height	8.40 in (21.336 cm)
Package 1 width	19.50 in (49.530 cm)
Package 1 Length	30.50 in (77.470 cm)

Offer Sustainability

Sustainable offer status	Green Premium product
California proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov
REACH free of SVHC	Yes
EU RoHS Directive	Compliant EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration
Environmental Disclosure	Product Environmental Profile
PVC free	Yes

Contractual warranty

Warranty	18 months
----------	-----------