

High Security Shredders

NSA/CSS O2-01 High Security Shredders



Dahle High Security Shredders offer the greatest protection available. These machines are designed for military, federal, state or local governments as well as Department of Defense contractors engaged in projects where National Security is an issue.

EvenFlow Lubricator

Just like any fine-tuned machine, your shredder needs to be properly oiled to run at peak performance. Each High Security shredder is equipped with an automatic oiler that provides slow, continuous oil across the entire cutting mechanism.

Precision Milled Cylinders

These shredders features solid cutting cylinders milled from a bar of German Solingen steel. The result is a machine with strength, power and the ability to handle all of your top-secret data destruction needs.

SmartPower

This intuitive system reduces power consumption after ten minutes of sitting idle (sleep mode), and completely powers down after 30 minutes of inactivity. Dahle SmartPower conserves energy as well as reduces electrical costs (excludes 20394).

Jam Protection

Fewer things are more frustrating than a paper jam. With automatic jam protection, these shredders prevent those annoyances. If sheet capacity is exceeded, the motor automatically stops and reverses to push the paper back out. This prevents a jam and makes it easy to re-feed fewer sheets.

DAHLE CleanTEC®

Some models are available with fine dust filtration, this system permanently traps up to 98% of the fine dust and provides a cleaner, healthier work environment.



20434ds

Security Level: P-7
Sheet Capacity: 4 / 6
Waste Volume: 6 gal.
NSA Volume Rating: Low
w/Deployment Case



40334 / 41334

Security Level: P-7
Sheet Capacity: 5 / 7
Waste Volume: 23 gal.
NSA Volume Rating: Med.
w/EvenFlow Lubricator



40434 / 41434

Security Level: P-7
Sheet Capacity: 8 / 10
Waste Volume: 30 gal.
NSA Volume Rating: High
w/EvenFlow Lubricator



40534 / 41534

Security Level: P-7
Sheet Capacity: 8 / 10
Waste Volume: 38 gal.
NSA Volume Rating: High
w/EvenFlow Lubricator



20394

Security Level: P-7
Sheet Capacity: 9 / 11
Waste Volume: 50 gal.
NSA Volume Rating: High
w/EvenFlow Lubricator

Specifications

Model	Security Level	Capacity #20 / #16	Shred Size	Waste Volume	Feed Width	Speed feet/min	Decibel Level	NSA Volume Rating	Features				Warranty Shredder / Cylinders	Dimensions length x width x height
									CleanTEC®	Jam Protection	Smart Power	Auto Oiler		
20434ds	P-7	4 / 6	1mm x 4.7mm	6 gal.	9 1/2"	13 f/m	50 dB	Low		•			2 years / 1 year	14" x 16" x 18"
40334	P-7	5 / 7	1mm x 4.7mm	23 gal.	10 1/4"	22 f/m	50 dB	Medium		•	•	•	2 years / 1 year	18 1/4" x 21 1/2" x 34 1/4"
41334	P-7	5 / 7	1mm x 4.7mm	23 gal.	10 1/4"	22 f/m	50 dB	Medium	•	•	•	•	2 years / 1 year	18 1/4" x 21 1/2" x 34 1/4"
40434	P-7	8 / 10	1mm x 4.7mm	30 gal.	10 1/4"	22 f/m	52 dB	High		•	•	•	2 years / 1 year	18 1/4" x 21 1/2" x 36 3/4"
41434	P-7	8 / 10	1mm x 4.7mm	30 gal.	10 1/4"	22 f/m	52 dB	High	•	•	•	•	2 years / 1 year	18 1/4" x 21 1/2" x 36 3/4"
40534	P-7	8 / 10	1mm x 4.7mm	38 gal.	12"	23 f/m	52 dB	High		•	•	•	2 years / 1 year	21" x 29" x 34 1/2"
41534	P-7	8 / 10	1mm x 4.7mm	38 gal.	12"	23 f/m	52 dB	High	•	•	•	•	2 years / 1 year	21" x 29" x 34 1/2"
20394	P-7	9 / 11	1mm x 4.7mm	50 gal.	16"	35 f/m	56 dB	High				•	2 years / 1 year	24 1/2" x 29 1/2" x 46 3/4"

All performance data has been established using #20 / #16 bond 8 1/2" x 11" paper. Different paper qualities may yield different results.



Dahle North America, Inc.

49 Vose Farm Road

Peterborough, NH 03458

(800) 995.1379 / www.dahle.com

