

# Product data sheet

## Characteristics

# HOM24L70F

Load center, Homeline, 1 phase, 2 spaces, 4 circuits, 70A fixed main lugs, NEMA1, flush cover



### Main

Product Type	Load Center
Marketing Trade Name	Homeline
Load Center Type	Main lugs
Rated Current	70 A
Number of Spaces	2
Maximum Number of Single Pole Circuits	4
Enclosure Rating	NEMA 1 for indoor NEMA 3R for outdoor
Cover Type	Flush cover
Electrical Connection	Lugs

### Complementary

Max Short Circuit Current Rating	10 kA
Maximum Number of Tandem Breakers	2
Number of Phases	1 phase
Voltage Rating	120/240 V AC
Wire Size	AWG 12...AWG 3 aluminium AWG 14...AWG 4 copper
Wiring Configuration	3-wire
Busbar Material	Tin plated aluminium busbar
Enclosure Material	Welded sheet steel
Surface Finish	Baked enamel grey
Box Number	2
Height	9.29 in (236 mm)
Depth	3.19 in (81 mm)
Width	4.80 in (122 mm)

### Environment

Ambient Air Temperature for Operation	23 °F (-5 °C) 104 °F (40 °C)
Product Certifications	UL listed file E-6294

### Ordering and shipping details

Category	00149 - HOM 2-8 CKT,MLO,NEMA1&3R
Discount Schedule	DE3C
GTIN	00785901061151
Nbr. of units in pkg.	1
Package weight(Lbs)	3.79 lb(US) (1.72 kg)
Returnability	Yes
Country of origin	MX

## Packing Units

Package 1 Height	4.10 in (10.414 cm)
Package 1 width	6.60 in (16.764 cm)
Package 1 Length	11.40 in (28.956 cm)

## Offer Sustainability

Sustainable offer status	Green Premium product
California proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to <a href="http://www.P65Warnings.ca.gov">www.P65Warnings.ca.gov</a>
REACH Regulation	<a href="#">REACH Declaration</a>
REACH free of SVHC	Yes
EU RoHS Directive	Compliant <a href="#">EU RoHS Declaration</a>
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	<a href="#">Yes</a>
China RoHS Regulation	<a href="#">China RoHS Declaration</a>
Environmental Disclosure	<a href="#">Product Environmental Profile</a>

## Contractual warranty

Warranty	Lifetime
----------	----------