



Main

Product range	8501N
Product type	Relay Socket
Pin shape	Tubular
Number of pins	8
[In] rated current	15 A 300 V AC 5 A 600 V AC

Complementary

Electrical connection	Single tiered screw clamp terminals
Mounting type	DIN rail Panel
Package quantity	Set of 10

Environment

Certifications	UL Recognized CSA CE
Height	2.13 in (54 mm)
Width	1.57 in (40 mm)
Depth	0.97 in (24.6 mm)

Ordering and shipping details

Category	21142 - 8501 N
Discount Schedule	CP2
GTIN	00785901006046
Nbr. of units in pkg.	1
Package weight(Lbs)	1 lb(US) (0.45 kg)
Returnability	Yes
Country of origin	CN

Packing Units

Unit Type of Package 1	PCE
Package 1 Height	1.00 in (2.54 cm)
Package 1 width	1.70 in (4.318 cm)
Package 1 Length	2.30 in (5.842 cm)
Unit Type of Package 2	CAR
Number of Units in Package 2	10
Package 2 Weight	14.56 oz (412.769 g)
Package 2 Height	1.70 in (4.318 cm)
Package 2 width	4.40 in (11.176 cm)
Package 2 Length	4.40 in (11.176 cm)

Offer Sustainability

Sustainable offer status	Green Premium product
California proposition 65	WARNING: This product can expose you to chemicals including: Nickel compounds, which is known to the State of California to cause cancer, and Di-isodecyl phthalate (DIDP), which is known to the State of California to cause birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration
Environmental Disclosure	Product Environmental Profile

Contractual warranty

Warranty	18 months
----------	-----------