



## Main

Product	Circuit breaker
Range	QO
Current Rating	150 A
Voltage Rating	120/240 V AC
Mounting Type	Bolt-on
Number of Poles	2P
Ratings	Primary main breaker
Electrical Connection	Lugs
Frame Size	QOM2

## Complementary

Interrupt Rating	10 kA 120/240 V AC 50/60 Hz
Wire Size	AWG 4...300 kcmil copper or aluminium
Tightening Torque	53.10 lbf.in (6 N.m) 0.01...0.10 in <sup>2</sup> (4...65 mm <sup>2</sup> ) (AWG 12...AWG 2/0)
Height	5.6 in (142.24 mm)
Width	5.07 in (128.78 mm)
Depth	3.6 in (91.44 mm)
Load Center Type	Main breaker
Number of Phases	1 phase
For Use With	QO load center

## Environment

Certifications	UL Listed CSA
Ambient Rating	104 °F (40 °C)

## Ordering and shipping details

Category	00024 - Q2 & QE METERING BREAKERS
Discount Schedule	DE2A
GTIN	00785901765219
Nbr. of units in pkg.	1
Package weight(Lbs)	2.59 lb(US) (1.17 kg)
Returnability	Yes
Country of origin	MX

## Packing Units

Unit Type of Package 1	PCE
Package 1 Height	4.30 in (10.922 cm)
Package 1 width	5.50 in (13.97 cm)
Package 1 Length	6.40 in (16.256 cm)
Unit Type of Package 2	PAL
Number of Units in Package 2	468
Package 2 Weight	1250.00 lb(US) (566.99 kg)
Package 2 Height	40.00 in (101.6 cm)

Package 2 width	40.00 in (101.6 cm)
Package 2 Length	48.00 in (121.92 cm)

### Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	<a href="#">REACH Declaration</a>
REACH free of SVHC	Yes
EU RoHS Directive	Compliant <a href="#">EU RoHS Declaration</a>
Mercury free	Yes
RoHS exemption information	<a href="#">Yes</a>
China RoHS Regulation	<a href="#">China RoHS Declaration</a>
Environmental Disclosure	<a href="#">Product Environmental Profile</a>

### Contractual warranty

Warranty	18 months
----------	-----------