



Main

Range	Spacial
Accessory / separate part category	Mounting accessory
Product or component type	Mounting plate
Device application	Multi-purpose
Enclosure nominal dimensions	31.50 in (800 mm) 39.37 in (1000 mm) 39.37 in (1000 mm) 31.50 in (800 mm)
Mounting location	Direct fixing on backstuds Step slide
Mounting plate description	Plain
Range compatibility	Spacial S3D Spacial CRN Spacial S3X Thalassa PLM
Quantity per set	Set of 1
Material	Galvanised steel

Complementary

Fixing mode	Screwed on backstuds M8 By fixing element
Permanent permissible load	330.69 lb(US) (150 kg)
Height	37.40 in (950 mm)
Width	29.53 in (750 mm)
Depth	4.92 in (125 mm)
Thickness	0.10 in (2.5 mm)
Net Weight	30.78 lb(US) (13.96 kg)
Variant particularity	Installation in enclosures with inverted dimensions

Ordering and shipping details

Category	80036 - ENCLOSURE SYSTEMS ACCESSORIES
Discount Schedule	ES1
GTIN	00785901627609
Nbr. of units in pkg.	1
Package weight(Lbs)	30.29 lb(US) (13.74 kg)
Returnability	Yes
Country of origin	ES

Packing Units

Package 1 Height	37.40 in (950.000 mm)
Package 1 width	29.72 in (755.000 mm)
Package 1 Length	0.59 in (15.000 mm)

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration
Environmental Disclosure	Product Environmental Profile

Contractual warranty

Warranty	18 months
----------	-----------