



### Main

Marketing Trade Name	QO
Product Type	Load Center
Cover Type	Surface cover

### Complementary

Tightening Torque	Main lugs 35 lb.in, AWG 14...AWG 10, aluminium/copper Main lugs 40 lb.in, AWG 8...AWG 4, aluminium/copper
Load Center Type	Main lugs
Rated Current	50 A
Number of Spaces	2
Max Short Circuit Current Rating	10 kA
Maximum Number of Single Pole Circuits	4
Maximum Number of Tandem Breakers	2
Number of Phases	1 phase
Voltage Rating	120/240 V AC
Wire Size	AWG 14...AWG 6 copper
Ground Bar	Grounding bar (factory installed)
Electrical Connection	Lugs
Wiring Configuration	2-wire
Busbar Material	Tin plated aluminium: busbar
Enclosure Material	Welded sheet steel
Box Number	2
Height	9.29 in (236 mm)
Width	4.80 in (122 mm)

### Environment

Enclosure Rating	NEMA 1 indoor
Ambient Air Temperature for Operation	23 °F (-5 °C) 104 °F (40 °C)
Product Certifications	CSA

### Ordering and shipping details

Category	00101 - QO 1PH LC,2-8CKT,NEMA 1,3R
Discount Schedule	DE3A
GTIN	00785901785163
Nbr. of units in pkg.	1
Package weight(Lbs)	3.33 lb(US) (1.51 kg)
Returnability	Yes
Country of origin	MX

## Packing Units

Package 1 Height	3.20 in (8.128 cm)
Package 1 width	5.10 in (12.954 cm)
Package 1 Length	9.60 in (24.384 cm)

## Offer Sustainability

California proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to <a href="http://www.P65Warnings.ca.gov">www.P65Warnings.ca.gov</a>
REACH Regulation	<a href="#">REACH Declaration</a>
REACH free of SVHC	Yes
EU RoHS Directive	Compliant <a href="#">EU RoHS Declaration</a>
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	<a href="#">Yes</a>
China RoHS Regulation	<a href="#">China RoHS Declaration</a>

## Contractual warranty

Warranty	18 months
----------	-----------