

B-634 Clear Polyester Laminating Tape

TDS No. B-634
Effective Date: 07/01/2011

Description:

Brady B-634 is a rigid, clear polyester overlamine for use with Brady ToughStripe labels.

Details:

General

Material Type: Clear Polyester (3 mil film)

Finish: Glossy

Adhesive: Permanent Rubber Based

Applications:

Brady B-634 is recommended for use as a clear protective overlamine for Brady ToughStripe labels.

Thickness (PSTC-33):

0.004 in. (0.10 mm)

Adhesive Properties:

Adhesion to Stainless Steel (PSTC-101)

15 Minute Dwell (Avg.) – 102.0 oz/in (111 N/100 mm)

Abrasion Resistance (Method 5306 of U.S. Federal Test Method Std. No. 191A):

H-22 Stone Wheels, 1000g wts.

Material withstands over 9000 cycles

S-35 Tungsten Carbide Wheels, 1000g wts.

Material withstands up to 1000 cycles

Gloss (60° Gardner):

115 Gardner Units

Minimum Application Temperature:

40°F (5°C)

Service Temperature:

0°F to 130°F (-18°C to 54°C)

Average Outdoor Durability:

Not recommended for outdoor use.

Chemical Resistance:

Samples were tested laminated over Brady B-483 flood coated polyester. Samples were allowed to dwell 24 hours at room temperature prior to testing. Testing was conducted at room temperature.

7 Day Immersion: Immersed in reagent for 7 days.

Dip Test: Five 10 minute dips in reagent with 30 minute recovery.

REAGENT	7 DAY IMMERSION	DIP TEST
30% Sulfuric Acid	NE	NE
10% Sulfuric Acid	NE	NE
30% Hydrochloric Acid	F	NE
10% Hydrochloric Acid	NE	NE
Glacial Acetic Acid	F	F
5% Acetic Acid	NE	NE
50% Sodium Hydroxide	F	F
10% Sodium Hydroxide	F	F
10% Ammonia	F	NE
5% Sodium Hypochlorite (bleach)	F	NE
10% Sodium Chloride	NE	NE

Methanol	F	NE
Isopropyl Alcohol	NE	NE
Heptane	F	NE
Mineral Spirits	F	F
Turpentine	F	NE
Diesel Fuel	NE	NE
Kerosene	F	NE
Gasoline	F	NE
ASTM #3 Oil	NE	NE
SAE 20 Oil	NE	NE
Alconox®	NE	NE
Water	NE	NE

NE = No Effect

NT = Not Tested

F = Failed (affected Sample)

Product testing, customer feedback, and history of similar products, support a customer performance expectation of at least **two years from the date of receipt** for this product as long as this product is stored in its original packaging in an environment *below 80°F (27°C) and 60% RH*. We are confident that our product will perform well beyond this time frame. However, it remains the responsibility of the user to assess the risk of using such product. We encourage customers to develop functional testing protocols that will qualify a product's fitness for use in their actual applications.

Trademarks:

ASTM: American Society for Testing and Materials (U.S.A.)

Alconox® is a registered trademark of Alconox Co.

Note: All values shown are averages and should not be used for specification purposes.

Test data and test results contained in this document are for general information only and shall not be relied upon by Brady customers for designs and specifications, or be relied on as meeting specified performance criteria. Customers desiring to develop specifications or performance criteria for specific product applications should contact Brady for further information.

Product compliance information is based upon information provided by suppliers of the raw materials used by Brady to manufacture this product or based on results of testing using recognized analytical methods performed by a third party, independent laboratory. As such, Brady makes no independent representations or warranties, express or implied, and assumes no liability in connection with the use of this information.

WARRANTY

Brady products are sold with the understanding that the buyers will test them in actual use and determine for themselves their adaptability to their intended uses. Brady warrants to the buyers that its products are free from defects in material and workmanship, but limits its obligation under this warranty to replacement of the product shown to Brady's satisfaction to have been defective at the time Brady sold it. This warranty does not extend to any persons obtaining the product from the buyers. This warranty is in lieu of any other warranty, express or implied, including, but not limited to, any implied warranty of merchantability or fitness for a particular purpose, and of any other obligations or liability on Brady's part. Under no circumstances will Brady be liable for any loss, damage, expense, or consequential damages of any kind arising in connection with the use, or inability to use, Brady's products.

Copyright 2016 Brady Worldwide, Inc. | All Rights Reserved
Material may not be reproduced or distributed in any form without written permission.