

Tripp Lite 1111 W. 35th Street Chicago, IL 60609 USA Telephone: 773.869.1234 www.tripplite.com

UL1363a, Paragraph 14.1(d) States "The SPRPT shall be permanently attached to the medical equipment by a means such that it is only removable with the use of a tool." To achieve compliance, one must use the PSCLAMP.


Safe-IT UL 1363A Medical-Grade Power Strip for Patient-Care Vicinity, 4x Hospital-Grade Outlets, 3 ft. Coiled Cord

MODEL NUMBER: PS-410-HGOEMCC









Versatile power strip with coiled cord supplies power to movable plug-connected components mounted to IV poles, mobile carts, crash carts and mobile medical workstations in operating rooms and patient-care vicinities.

Description

The PS-410-HGOEMCC Medical-Grade Power Strip supplies power to movable plug-connected components mounted to a rack, table or pedestal in operating rooms, patient-care vicinities, therapy rooms, imaging environments and administrative areas. Compliant with UL 1363A specifications, this 120V, 50/60 Hz power strip features a NEMA 5-15P-HG hospital-grade plug and four NEMA 5-15R-HG hospital-grade outlets.

The power strip is protected by a patented antimicrobial powder coating with EPA-registered and FDAcompliant silver ionic technology. The antimicrobial surface protection is 99.9 percent effective in inhibiting the growth of bacteria and reducing the risk of HAIs in hospitals and other medical environments. The coating meets the requirements of JIS Z 2801:2000, an international standard for evaluating efficacy in antimicrobial products.

Two built-in resettable 15A circuit breakers control power to all outlets and protect the power strip against overloads. Switchless design prevents the unit from being accidentally shut off. The coiled power cord is three feet (0.9 meters) long, and can be fully extended to 10 feet (3 m).

Mounting flanges let you install the PS-410-HGOEMCC on a wide variety of surfaces, such as IV poles, mobile carts, crash carts and mobile medical workstations. The all-metal housing ensures safety and is guaranteed to last a long time in demanding environments.

Features

Power Distribution Anywhere in Any Medical FacilityIdeal for use in operating rooms, patient-care vicinities, therapy rooms, imaging environments and administrative areasFor use on IV poles, mobile carts, crash carts and mobile workstations, when properly mounted120V, 50/60 Hz power strip complies with UL 1363A specifications

Exclusive, Patented Antimicrobial ProtectionSilver ionic powder coating is 99.9% effective in inhibiting the growth of bacteriaPatented coating helps to reduce the risk of healthcare-acquired infections (HAIs) in

Highlights

- Patented antimicrobial coating is 99.9% effective in inhibiting the growth of bacteria
- Approved for use in patient-care vicinities when properly mounted
- Complies with UL 1363A specifications
- 3 ft. (0.9 m) coiled cord with NEMA 5-15P-HG hospital-grade plug extends to 10 ft.
- Features 4 NEMA 5-15R-HG hospital-grade outlets

Package Includes

- PS-410-HGOEMCC UL 1363A Medical-Grade Power Strip with four 15A Hospital-Grade Outlets and 3-ft. (0.91 m) Coiled, Extendable Cord
- Owner's Manual with
 maintenance requirements



hospitals and other medical environmentsCoating meets the requirements of JIS Z 2801:2000, an international standard for evaluating efficacy in antimicrobial products

Versatile Medical-Grade Solution4 NEMA 5-15R-HG hospital-grade outlets provide consistent power3 ft. power cord is coiled so it can be extended up to 10 ft.Rugged, all-metal housing for long life in demanding environments

Premium Safety FeaturesDual, resettable built-in 15A circuit breakers protect against dangerous overloadsSwitchless design prevents accidental shut-off

Ready to Use Right Out of the BoxBuilt-in mounting flanges make the PS-410-HGOEMCC easy to install on a variety of surfaces

Specifications

OVERVIEW		
UPC Code	037332148834	
INPUT		
Nominal Input Voltage(s) Supported	120V AC	
Recommended Electrical Service	15A, 120V	
Input Plug Features	Coiled Hospital Grade Plug	
Input Cord Gauge Type	14 gauge; SJT	
Voltage Compatibility (VAC)	120	
Input Plug Type	NEMA 5-15P-HG	
Input Cord Length (ft.)	10	
Input Cord Length (m)	3.05	
Integrated Cord Clip	No	
OUTPUT		
Frequency Compatibility	50 / 60 Hz	
Output (Watts)	1800	
Output Receptacles	(4) 5-15R-HG	
Circuit Breaker (amps)	15	
Overload Protection	2 x 15amp breakers (1 line, 1 neutral)	
Transformer Accommodation	(2) Yes	
Outlet Orientation	Single row of 4	
Right-Angle Outlets	No	
USER INTERFACE, ALERTS & CONTROLS		
Switches	No power switch	
PHYSICAL		



Tripp Lite 1111 W. 35th Street Chicago, IL 60609 USA Telephone: 773.869.1234 www.tripplite.com

Color	White
Antimicrobial Coating	Yes
Color (AC Line Cord)	White
Form Factors Supported	IV poles, mobile carts, crash carts and mobile medical workstations
Included Mounting Accessories	Mounting tabs and flanges
Integrated Keyhole Mounting Slots	Yes (Includes flanges)
Keyhole Slot Mounting Measurement (Center to Center)	Distance between keyhole tabs = 127mm; Distance between end tabs = 207.45mm
Material of Construction	Metal
Outlets Measurement (Center to Center)	77.60mm
Receptacle Color	White
Shipping Dimensions (hwd / cm)	24.89 x 6.60 x 16.00
Shipping Dimensions (hwd / in.)	9.80 x 2.60 x 6.30
Shipping Weight (kg)	1.04
Shipping Weight (lbs.)	2.30
Unit Dimensions (hwd / cm)	4.39 x 6.35 x 21.69
Unit Dimensions (hwd / in.)	1.73 x 2.50 x 8.54
Unit Weight (kg)	1.00
Unit Weight (lbs.)	2.20
SPECIAL FEATURES	
Built-in Cable Management	No
STANDARDS & COMPLIANCE	
Approvals	TUV tested to UL 1363A
WARRANTY	
Product Warranty Period (Worldwide)	Lifetime limited warranty

© 2021 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: https://www.tripplite.com/products/product-certification-agencies