



### Main

Range	ClimaSys
Product name	ClimaSys CC
Product or component type	Double thermostat
Temperature setting range	32...140 °F (0...60 °C)
Information displayed	Temperature in °C

### Complementary

Input voltage	250 V
Sensor type	Bimetal
Contacts type and composition	1 NO/NC
Contact resistance	10 mOhm
Service life in cycles	100000 cycles
Maximum switching capacity	2 A 120...250 V AC inductive 0.6 10 A 250 V AC resistive 15 A 120 V AC resistive 30 W DC
Electrical connection	4 terminals, clamping capacity: 2.5 mm <sup>2</sup>
Mounting mode	Clipped
Height	External 2.68 in (68 mm)
Width	External 2.20 in (56 mm)
Depth	External 1.73 in (44 mm)
Net Weight	1.41 oz (40 g)
Mounting location	Spacial upright On mounting plate 35 mm DIN rail Cross rails
Ambient air temperature for operation	-4...176 °F (-20...80 °C)
IP degree of protection	IP20
Hysteresis	7 %
Number of outputs	1 heating function 1 ventilation function
Material	PC
Color	Light gray
Flame retardance	Self-extinguishing conforming to UL94 (material V0)
Product certifications	UL

### Ordering and shipping details

Category	80036 - ENCLOSURE SYSTEMS ACCESSORIES
Discount Schedule	ES1
GTIN	00785901846321
Nbr. of units in pkg.	1
Package weight(Lbs)	0.24 lb(US) (0.11 kg)
Returnability	Yes
Country of origin	FR

## Packing Units

Unit Type of Package 1	PCE
Package 1 Height	2.36 in (6 cm)
Package 1 width	2.76 in (7 cm)
Package 1 Length	3.15 in (8 cm)

## Offer Sustainability

California proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to <a href="http://www.P65Warnings.ca.gov">www.P65Warnings.ca.gov</a>
REACH Regulation	<a href="#">REACH Declaration</a>
REACH free of SVHC	Yes
EU RoHS Directive	Compliant <a href="#">EU RoHS Declaration</a>
Mercury free	Yes
RoHS exemption information	<a href="#">Yes</a>
China RoHS Regulation	<a href="#">China RoHS Declaration</a>

## Contractual warranty

Warranty	18 months
----------	-----------