

8538SCG13V02S

NEMA Combination Starter, Type S, 60A
fusible disconnect, Size 1, 27A, 7.5 HP at 240
VAC polyphase, 120 VAC coil, NEMA 1



Main

Product	Combination Starter
Type	S
Control Circuit Type	Separate control circuit

Complementary

Control Circuit Voltage	110 V AC 50 Hz 120 V AC 60 Hz
Starter Type	Non reversing
Number of Poles	3P
Horsepower Rating	7.5 Hp 200 V AC, 3 phase 7.5 hp 230 V AC, 3 phase
Maximum Voltage Rating	600 V AC
Control Units	No control units
Pilot Light	No indicator
Auxiliary Contacts	Without
Thermal overload type	Melting alloy 3
Disconnect Type	Fusible disconnect switch H, 60 A
NEMA size	1

Environment

Enclosure Type	NEMA 1 painted sheet steel with external reset
----------------	--

Ordering and shipping details

Category	21213-8538,39 SC,SD(NOT S*R,T,W)
Discount Schedule	CP1
GTIN	00785901743774
Package weight(Lbs)	32.57 lb(US) (14.774 kg)
Returnability	No
Country of origin	MX

Packing Units

Package 1 Height	10.50 in (26.670 cm)
Package 1 width	10.30 in (26.162 cm)
Package 1 Length	27.00 in (68.580 cm)

Offer Sustainability

California proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov
EU RoHS Directive	Not compliant
China RoHS Regulation	China RoHS Declaration

Contractual warranty

Warranty	18 months
----------	-----------