



Main

Product or component type	Shunt trip
Circuit breaker type	M-frame R-Frame P-frame

Complementary

Rated voltage	220...240 V AC 250 V DC
Tightening torque	30.98 lbf.in (3.5 N.m)

Environment

Product certifications	CSA
------------------------	-----

Ordering and shipping details

Category	01250 - M,P,R FRAME ACCESSORIES ONLY
Discount Schedule	DE2
GTIN	00785901899136
Nbr. of units in pkg.	1
Package weight(Lbs)	0.5 lb(US) (0.23 kg)
Returnability	Yes
Country of origin	US

Packing Units

Package 1 Height	1.50 in (3.810 cm)
Package 1 width	3.00 in (7.620 cm)
Package 1 Length	5.00 in (12.700 cm)

Offer Sustainability

California proposition 65	WARNING: This product can expose you to chemicals including: DINP, which is known to the State of California to cause cancer, and DIDP, which is known to the State of California to cause birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration

Contractual warranty

Warranty	18 months
----------	-----------