

# Product data sheet

## Characteristics

# QOC20UFWGW

Cover, QO, load center, 20 circuits, flush, wide gutter, white



### Main

Marketing Trade Name	QO
Product Type	Load Center Cover

### Complementary

Cover Type	Flush cover
Product Compatibility	For indoor load center
Surface Finish	Baked enamel White
Number of Spaces	20
Height	22.13 in (562.10 mm)
Width	15.44 in (392.18 mm)
Depth	0.7 in (17.78 mm)
Tightening Torque	Cover 2.3 N.m

### Ordering and shipping details

Category	00167 - DE3A MISC
Discount Schedule	DE3A
GTIN	00785901085843
Nbr. of units in pkg.	1
Package weight(Lbs)	1 lb(US) (0.45 kg)
Returnability	Yes

### Offer Sustainability

REACH Regulation	<a href="#">REACH Declaration</a>
REACH free of SVHC	Yes
EU RoHS Directive	Compliant <a href="#">EU RoHS Declaration</a>
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	<a href="#">Yes</a>
China RoHS Regulation	<a href="#">China RoHS Declaration</a>

### Contractual warranty

Warranty	18 months
----------	-----------