

# Product data sheet

## Characteristics

# 8903SQO10V02

Contactor, Type S, multipole lighting,  
mechanically held, 100A, 2 pole, 110/120 V  
50/60 Hz coil, 600 VAC, open



### Main

Product	Mechanically Held Lighting Contactor
Type	S

### Complementary

Control Circuit Voltage	120 V AC 60 Hz 110 V AC 50 Hz
Current Rating	100 A
Number of Poles	2P
Control Units	No control units
Pilot Light	Without pilot light
Auxiliary Contacts	Without
Other Options	None
Electrical connection	Lugs
Height	7.24 in (184 mm)
Depth	6.73 in (171 mm)
Width	5.94 in (151 mm)

### Environment

Enclosure Type	Not rated (open device) surface none
Product certifications	UL Listed CSA

### Ordering and shipping details

Category	21324 - 8903 S (NOT S°C) MECH.
Discount Schedule	CP1
GTIN	00785901861980
Nbr. of units in pkg.	1
Package weight(Lbs)	17.88 lb(US) (8.11 kg)
Returnability	No
Country of origin	MX

### Packing Units

Package 1 Height	9.50 in (24.130 cm)
Package 1 width	13.80 in (35.052 cm)
Package 1 Length	18.00 in (45.720 cm)

## Offer Sustainability

California proposition 65	WARNING: Cancer and Reproductive Harm - <a href="http://www.P65Warnings.ca.gov">www.P65Warnings.ca.gov</a>
EU RoHS Directive	Not compliant
China RoHS Regulation	 <a href="#">China RoHS Declaration</a>

## Contractual warranty

Warranty	18 months
----------	-----------