

Product data sheet

Characteristics

HOM2040M100PQCVP

Load center, Homeline, 1 phase, 20 spaces, 40 circuits, 100A convertible main breaker, PoN, NEMA1, Qwik-grip, value pack



Main

Product Type	Load Center value pack
Marketing Trade Name	Homeline
Load Center Type	Main breaker
Rated Current	100 A
Number of Spaces	20
Maximum Number of Single Pole Circuits	40
Enclosure Rating	NEMA 1 for indoor
Cover Type	Combination flush/surface cover
Electrical Connection	Lugs
Provided Equipment	Circuit breaker 2) 1P 20 A 120/240 V AC Circuit breaker 1) 2P 100 A 120/240 V AC main supply ready assembled Circuit breaker 1) 2P 30 A 120/240 V AC Load center 1) Qwik grip assembly kit 1)

Complementary

Max Short Circuit Current Rating	10 kA
Maximum Number of Tandem Breakers	20
Number of Phases	1 phase
Voltage Rating	120/240 V AC
Wire Size	AWG 6...AWG 2/0 aluminium AWG 6...AWG 1 copper
Ground Bar	Grounding bar (ordered separately)
Wiring Configuration	3-wire
Enclosure Material	Welded galvanized steel
Surface Finish	Baked enamel grey
Box Number	6
Height	17.91 in (455 mm)
Depth	3.74 in (95 mm)
Width	14.25 in (362 mm)

Environment

Ambient Air Temperature for Operation	23 °F (-5 °C) 104 °F (40 °C)
---------------------------------------	---------------------------------

Ordering and shipping details

Category	00185 - MISC. HOM LOAD CENTERS
Discount Schedule	DE3C
GTIN	00785901639343
Nbr. of units in pkg.	1
Package weight(Lbs)	22.64 lb(US) (10.27 kg)
Returnability	Yes
Country of origin	US

Packing Units

Package 1 Height	5.50 in (13.970 cm)
Package 1 width	16.00 in (40.640 cm)
Package 1 Length	23.30 in (59.182 cm)

Offer Sustainability

California proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov
REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Compliant EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration