

Product data sheet

Characteristics

QMB322TD

Fusible Switch, QMB, 60 A to 60 A, 240 VAC, 3 pole, 7.5 hp, 4.5 in



Main

Product or component type	Fuse-switch disconnecter
Number of poles	3
[Ue] rated operational voltage	240 V AC
Line Rated Current	60 A - 60 A 240 V AC

Complementary

Height	4.49 in (114 mm)
Number of modules	2

Environment

Product certifications	CSA UL
------------------------	-----------

Ordering and shipping details

Category	00037 - QMB BRANCH CB,SW,& MAIN SW
Discount Schedule	PE1A
GTIN	00785901535928
Nbr. of units in pkg.	1
Package weight(Lbs)	17.66 lb(US) (8.01 kg)
Returnability	Yes
Country of origin	US

Packing Units

Package 1 Height	5.20 in (13.208 cm)
Package 1 width	12.50 in (31.750 cm)
Package 1 Length	25.50 in (64.770 cm)

Offer Sustainability

California proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov
REACH free of SVHC	Yes
EU RoHS Directive	Compliant EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration
PVC free	Yes

Contractual warranty

Warranty	18 months
----------	-----------
