

Product data sheet

Characteristics

VLSH2H5R

Disconnect switch, TeSys VLS, protruding rotary handle, hole mounting, 65x65mm, red handle, 5mm shaft



Main

Range	TeSys
Device short name	VLSH
Product or component type	Rotary handle
Range compatibility	TeSys VARIO LS VLS3P
Handle colour	Red
Handle front plate colour	Yellow
Rotary handle padlocking	1 to 3 padlocks 0.16...0.31 in (4...8 mm)
Marking	0 - 1 OFF-ON

Complementary

Fixing mode	Hole 0.89 in (22.5 mm)
Tightening torque	20.36 lbf.in (2.3 N.m)
Base dimension	65 x 65 mm
Height	2.56 in (65 mm)
Width	2.56 in (65 mm)
Depth	2.85 in (72.5 mm)
Net Weight	0.15 lb(US) (0.068 kg)

Environment

IP degree of protection	IP65
NEMA degree of protection	NEMA 1 NEMA 2 UL 508 NEMA 3R UL 508 NEMA 4 UL 508 NEMA 4X UL 508 NEMA 12 UL 508 NEMA 12K UL 508

Ordering and shipping details

Category	21734 - TESYS VLS DISCONNECT SWITCHES
Discount Schedule	CP1
GTIN	00785901575948
Nbr. of units in pkg.	1
Package weight(Lbs)	0.14 lb(US) (0.06 kg)
Returnability	Yes
Country of origin	IT

Packing Units

Unit Type of Package 1	PCE
Package 1 Height	2.56 in (6.5 cm)
Package 1 width	2.56 in (6.5 cm)
Package 1 Length	2.56 in (6.5 cm)
Unit Type of Package 2	S02
Number of Units in Package 2	40

Package 2 Weight	58.86 lb(US) (26.7 kg)
Package 2 Height	5.91 in (15 cm)
Package 2 width	11.81 in (30 cm)
Package 2 Length	15.75 in (40 cm)

Offer Sustainability

REACH free of SVHC	Yes
EU RoHS Directive	Compliant EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration