

Product data sheet

Characteristics

NSYTBP342912
 PC box IP66 IK08 RAL7035
 Int.H325W275D120 Ext.H341W291D128
 opaque PC cover H20



Main

Range	Thalassa
Product name	Thalassa TBP
Device application	Multi-purpose
Category	Industrial box
Height	13.43 in (341 mm)
Width	11.46 in (291 mm)
Depth	5.04 in (128 mm)
Internal height	12.80 in (325 mm)
Internal width	10.83 in (275 mm)
Internal depth	4.72 in (120 mm)
Enclosure mounting	Wall mounted
Device composition	1 body 1 cover 4 cover screw
Body type	One piece moulded
Type of front cover	Low plain cover
Cover fixing	Plastic screws
Lock type	Captive screw flat outside sealed area
Removable parts	Cover by captive screws

Complementary

Material	polycarbonate
Color	Gray RAL 7035)
Standards	IEC 62208 UL 508 A
Product certifications	TÜV UL
Electrical insulation class	Class II
Mounting location	Outdoor
Net Weight	2.56 lb(US) (1.16 kg)

Environment

IP degree of protection	IP66 conforming to NEMA 4.4X
IK degree of protection	IK08 conforming to IEC 62262
Fire resistance	1760 °F (960 °C)
Ambient air temperature for storage	5...140 °F (-15...60 °C)
Operating temperature	-13...176 °F (-25...80 °C)

Ordering and shipping details

Category	80033 - ENCLOSURE SYSTEMS POLYESTER
Discount Schedule	ES1
GTIN	00785901927655
Nbr. of units in pkg.	1
Package weight(Lbs)	3.01 lb(US) (1.37 kg)
Returnability	Yes
Country of origin	HU

Packing Units

Package 1 Height	5.04 in (128.000 mm)
Package 1 width	11.46 in (291.000 mm)
Package 1 Length	13.43 in (341.000 mm)

Offer Sustainability

REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration

Contractual warranty

Warranty	18 months
----------	-----------