

## NOT for Patient-Care Rooms - UL1363 Hospital-Grade Surge Protector with 6 Hospital-Grade Outlets, 6 ft. (1.83 m) Cord, 1050 Joules

MODEL NUMBER: **SPS606HGRA**



### Highlights

- 6 hospital-grade outlets
- 1050 joule rating
- 6-ft. cord with molded right angle hospital-grade plug
- All metal housing

### Package Includes

- SPS606HGRA Surge Suppressor
- Instruction manual with warranty information

Need to use a surge suppressor behind a desk or in a confined spot? The SPS606HGRA provides surge suppression with the convenience of a space-saving, right-angle hospital-grade plug for placing the units in confined areas and keyhole mounting tabs and flanges for easy installation.

### Features

- 1050-joule AC surge suppression rating
- Rugged all-metal housing withstands years of use without loss of ground path continuity
- 6 NEMA5-15R Hospital-Grade AC outlets
- 6-ft. AC cord with integrated, molded Hospital-Grade NEMA 5-15PHG plug
- Keyhole mounting tabs and flanges
- Switch safety cover prevents accidental shutoff
- 15A electrical capacity with built-in resettable circuit breaker
- 120 volt, 50/60Hz electrical compatibility
- Certified by UL (USA) and cUL (Canada)
- UL1449 3rd Edition listed
- Automatic shutoff permanently cuts power to outlets if protection circuit is incapacitated, preventing equipment damage and indicating replacement is required

## Specifications



UPC Code	037332167088
<b>INPUT</b>	
Nominal Input Voltage(s) Supported	120V AC
Recommended Electrical Service	120V (110-125V)
Voltage Compatibility (VAC)	120
Maximum Surge Amps	19500
Input Plug Type	NEMA 5-15P-HG
Input Cord Length (ft.)	6
Right-Angle Plug	Yes
Input Cord Length (m)	1.83
Integrated Cord Clip	No
<b>OUTPUT</b>	
Frequency Compatibility	50 / 60 Hz
Output (Watts)	1800
Output Receptacles	(6) 5-15R-HG
Circuit Breaker (amps)	15
Transformer Accommodation	(2) Yes
Right-Angle Outlets	No
<b>USER INTERFACE, ALERTS &amp; CONTROLS</b>	
Diagnostic LED(s)	Yes
Diagnostic LED Details	LINE POWER PRESENT (green)
Locking Switch Cover	Locking switch cover
<b>SURGE / NOISE SUPPRESSION</b>	
AC Suppression Joule Rating	1050
AC Suppression Response Time	< 1 ns
Protection Modes	Includes full normal mode surge suppression
Clamping Voltage (RMS)	140
Automatic Shut-Off	Yes
<b>DATALINE SURGE SUPPRESSION</b>	
Telephone/DSL Protection	No
Cable (Coax) Protection	No
Network (Ethernet) Protection	No



**Tripp Lite**  
1111 W. 35th Street  
Chicago, IL 60609 USA  
Telephone: 773.869.1234  
www.tripplite.com

<b>PHYSICAL</b>	
Color	White
Antimicrobial Coating	No
Color (AC Line Cord)	Light Gray
Integrated Keyhole Mounting Slots	Yes
Material of Construction	Metal
Receptacle Color	White
Shipping Dimensions (hwd / cm)	5.59 x 37.85 x 17.02
Shipping Dimensions (hwd / in.)	2.20 x 14.90 x 6.70
Shipping Weight (kg)	1.09
Shipping Weight (lbs.)	2.40
Unit Dimensions (hwd / cm)	3.81 x 34.9 x 6.35
Unit Dimensions (hwd / in.)	1.5 x 13.75 x 2.5
Unit Weight (kg)	1.45
Unit Weight (lbs.)	3.20
<b>SPECIAL FEATURES</b>	
Rotatable Outlets	No
<b>STANDARDS &amp; COMPLIANCE</b>	
Canada	cUL (Series Number: AGIB12015SL)
UL1449 3rd Edition (AC Suppression)	UL1449 3rd Edition (Series Number: AGIB12015SL)
UL1363 (Power Tap)	UL1363 (Series Number: AGIB12015SL)
<b>WARRANTY</b>	
Product Warranty Period (Worldwide)	Lifetime limited warranty

© 2021 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <https://www.tripplite.com/products/product-certification-agencies>