

Dahle 20392 Shredder

High Capacity Shredder



Product Features

EvenFlow Lubrication System

- Provides continuous oil across the cutting cylinders
- Ensures peak shredding performance

Precision Milled Cutting Cylinders

- Milled from a solid bar of steel for durability
- Ensures a perfectly matched set of cylinders

Automatic Jam Protection

- Reduces paper jams and eliminates frustration
- Prevents shredder down time

Chain Driven Motor

- Steel chain and gears for slip-free power
- Maximizes sheet capacity and performance

German Engineered

- Quality build with trouble free operation

User-Friendly Convenience Features

- Automatic On/Off for quick & easy power up
- Bin Full Auto-Off for bag change notification

The Dahle 20392 High Capacity Shredder supports the high-volume shredding needs of busy offices and departments. It features a powerful chain driven motor, an automatic EvenFlow Lubricator, and integrated jam protection to eliminate frustration. This P-5 shredder produces a 1/13" x 9/16" particle size and holds up to 50 gallons of shredded waste. It's German engineered and guaranteed to provide many years of trouble free operation.

AUTOMATIC OILER

Just like any fine-tuned machine, your shredder needs to be properly oiled to run at peak performance. This shredder is equipped with an EvenFlow Lubricator which provides slow, continuous oil across the entire cutting mechanism.

MILLED CYLINDERS

This shredder features solid cutting cylinders milled from a bar of German Solingen steel. They're perfectly aligned in an all-steel frame and guaranteed for life. The result is a machine with strength, power and the ability to handle all of your data destruction needs.

JAM PROTECTION

Fewer things are more frustrating than a paper jam. With automatic jam protection, this shredder prevents those annoyances. If sheet capacity is exceeded, the motor automatically stops and reverses to push the paper back out. This prevents a jam and makes it easy to re-feed fewer sheets



The 1 gallon EvenFlow Lubricator provides continuous lubrication for peak performance.



The cutting cylinders are milled from a solid bar of German Solingen steel for strength.

20392 Specifications

Feed Width	Capacity #20 / #16	Security Level	Shred Size	Waste Volume	Speed feet/min	Decibel Level	
16"	26 / 28	P-5	1/13" x 9/16"	50 gal	22 f/m	60 dB	
Special Features				Warranty		Dimensions	Weight
Staples/ Clips	CDs/ DVDs	Thermal Motor	Bin-Full Auto Off	Shredder	Cylinders	24.5" x 29.5" x 46.75"	359 lbs
●	●	●	●	2 years	Lifetime		

Performance data established using #20 / #16 bond 8 1/2" x 11" paper. Different paper qualities may yield different results.



Dahle North America, Inc.
49 Vose Farm Road
Peterborough, NH 03458
(800) 995.1379 / www.dahle.com

