



Main

Product or component type	Dry Sealed Transformer
Primary to Secondary Voltage	240 x 480 V 120/240 V
Full Capacity Taps	0

Complementary

Enclosure Code	15B
Phase	1 phase
Power Rating	25 kVA
Temperature rise	115 °C
Height	20 in (508.00 mm)
Width	15 in (381.00 mm)
Depth	13.5 in (342.90 mm)
Enclosure mounting	Wall mounted
Enclosure material	Painted sheet steel

Environment

Enclosure Type	NEMA 3R
Insulation temperature	356 °F (180 °C)
Product certifications	CULus UL Listed CSA

Ordering and shipping details

Category	16277 - RESIN LVGP XFMR
Discount Schedule	PE2
GTIN	00785901225430
Nbr. of units in pkg.	1
Package weight(Lbs)	385 lb(US) (174.63 kg)
Returnability	Yes
Country of origin	US

Packing Units

Package 1 Height	16.00 in (40.640 cm)
Package 1 width	19.30 in (49.022 cm)
Package 1 Length	15.30 in (38.862 cm)

Offer Sustainability

Sustainable offer status	Green Premium product
California proposition 65	WARNING: This product can expose you to chemicals including: Phenyl glycidyl ether, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov
REACH free of SVHC	Yes
EU RoHS Directive	Compliant EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration
Environmental Disclosure	Product Environmental Profile
PVC free	Yes

Contractual warranty

Warranty	18 months
----------	-----------