



## Main

|              |                                |
|--------------|--------------------------------|
| Product Type | Industrial Control Transformer |
| Power Rating | 200 VA                         |
| Type         | T                              |

## Complementary

|                                |                       |
|--------------------------------|-----------------------|
| Number of Phases               | 1 phase               |
| Power Rating                   | 200 VA                |
| Temperature Rise               | 80 °C                 |
| Electrical Connection          | Screw clamp terminals |
| Height                         | 3.2 in (81.28 mm)     |
| Width                          | 3.75 in (95.25 mm)    |
| Depth                          | 3.59 in (91.19 mm)    |
| Material                       | Copper winding        |
| Fingersafe Cover Compatibility | FSC1                  |

## Environment

|                        |  |
|------------------------|--|
| Certifications         | UL listed file E61239<br>CSA file LR37055 guide 184-N-90 |
| Enclosure Type         | Not rated (open device)                                  |
| Insulation Temperature | 266 °F (130 °C)  |

## Ordering and shipping details

|                       |                                  |
|-----------------------|----------------------------------|
| Category              | 16200 - 9070 T (NOT TF) 50-200VA |
| Discount Schedule     | CP8                              |
| GTIN                  | 00785901301103                   |
| Nbr. of units in pkg. | 1                                |
| Package weight(Lbs)   | 5.59 lb(US) (2.54 kg)            |
| Returnability         | Yes                              |
| Country of origin     | MX                               |

## Packing Units

|                  |                     |
|------------------|---------------------|
| Package 1 Height | 4.10 in (10.414 cm) |
| Package 1 width  | 4.20 in (10.668 cm) |
| Package 1 Length | 3.60 in (9.144 cm)  |

## Offer Sustainability

|                            |   |
|----------------------------|---|
| Sustainable offer status   | Green Premium product   |
| California proposition 65  | WARNING: This product can expose you to chemicals including: Phenyl glycidyl ether, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to <a href="http://www.P65Warnings.ca.gov">www.P65Warnings.ca.gov</a> |
| EU RoHS Directive          | Compliant <a href="#">EU RoHS Declaration</a>   |
| Mercury free               | Yes   |
| RoHS exemption information | <a href="#">Yes</a>   |
| China RoHS Regulation      | <a href="#">China RoHS Declaration</a>  |
| Environmental Disclosure   | <a href="#">Product Environmental Profile</a>   |
| PVC free                   | Yes   |

## Contractual warranty

|          |           |
|----------|-----------|
| Warranty | 18 months |
|----------|-----------|