



## Main

Product or component type	Electrically Held Lighting Contactor
Range of product	8903L
Control Circuit	Separate control circuit

## Complementary

Control Circuit Voltage	110 V AC 50 Hz 120 V AC 60 Hz
Inrush power in VA	180 VA 60 Hz 150 VA 50 Hz
Hold-in power consumption in VA	35 VA 60 Hz 35 VA 50 Hz
Current Rating	20 A tungsten 30 A fluorescent
Number of Poles	12P 12 NO
Control Unit	No control units
Pilot Light	No indicator
Electrical connection	Screw-clamp terminals
Height	16.30 in (414 mm)
Depth	8.62 in (219 mm)
Width	9.84 in (250 mm)

## Environment

Enclosure Type	NEMA 3R painted sheet steel surface
Product certifications	UL Listed CSA

## Ordering and shipping details

Category	21321 - 8903 L (NOT LX)
Discount Schedule	CP1
GTIN	00785901022862
Nbr. of units in pkg.	1
Package weight(Lbs)	19.44 lb(US) (8.82 kg)
Returnability	No
Country of origin	MX

## Packing Units

Package 1 Height	11.00 in (27.940 cm)
Package 1 width	10.20 in (25.908 cm)
Package 1 Length	16.70 in (42.418 cm)

## Offer Sustainability

Sustainable offer status	Green Premium product
REACH free of SVHC	Yes
EU RoHS Directive	Compliant <a href="#">EU RoHS Declaration</a>
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	<a href="#">Yes</a>
China RoHS Regulation	<a href="#">China RoHS Declaration</a>
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
PVC free	Yes
Halogen content performance	Halogen free plastic parts product

## Contractual warranty

Warranty	18 months
----------	-----------