

# Product data sheet

## Characteristics

# 8903LG40V04

Contactor, Type L, multipole lighting,  
electrically held, 30A, 4 pole, 600 V, 277 VAC  
60 Hz coil, NEMA 1



### Main

Product or component type	Electrically Held Lighting Contactor
Range of product	8903L
Control Circuit	Separate control circuit

### Complementary

Control Circuit Voltage	277 V AC 60 Hz
Inrush power in VA	150 VA 60 Hz
Hold-in power consumption in VA	30 VA 60 Hz
Current Rating	20 A tungsten 30 A fluorescent
Number of Poles	4P 4 NO
Control Unit	No control units
Pilot Light	No indicator
Electrical connection	Screw-clamp terminals
Height	12.68 in (322 mm)
Depth	6.02 in (153 mm)
Width	7.80 in (198 mm)

### Environment

Enclosure Type	NEMA 1 painted sheet steel surface
Product certifications	UL Listed CSA

### Ordering and shipping details

Category	21321 - 8903 L (NOT LX)
Discount Schedule	CP1
GTIN	00785901625650
Nbr. of units in pkg.	1
Package weight(Lbs)	9.64 lb(US) (4.37 kg)
Returnability	Yes
Country of origin	MX

### Packing Units

Package 1 Height	7.50 in (19.050 cm)
Package 1 width	8.20 in (20.828 cm)
Package 1 Length	13.00 in (33.020 cm)

## Offer Sustainability

Sustainable offer status	Green Premium product
REACH free of SVHC	Yes
EU RoHS Directive	Compliant <a href="#">EU RoHS Declaration</a>
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	<a href="#">Yes</a>
China RoHS Regulation	<a href="#">China RoHS Declaration</a>
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
PVC free	Yes
Halogen content performance	Halogen free plastic parts product

## Contractual warranty

Warranty	18 months
----------	-----------