

# Product data sheet

## Characteristics

# QO130L200PQG

Load center, QO, 1 phase, 30 spaces, 30 circuits, 200A convertible main lugs, PoN, NEMA1, Qwik-grip, gnd bar, UL



### Main

|                      |                           |
|----------------------|---------------------------|
| Marketing Trade Name | QO                        |
| Product Type         | Load Center               |
| Provided Equipment   | Qwik grip assembly kit 1) |

### Complementary

|  |   |
|--|---|
| Tightening Torque                      | Main lugs: 250 lb.in, AWG 4...250 kcmil, aluminium/copper |
| Load Center Type                       | Main lugs   |
| Rated Current                          | 200 A   |
| Number of Spaces                       | 30  |
| Max Short Circuit Current Rating       | 65 kA   |
| Maximum Number of Single Pole Circuits | 40  |
| Maximum Number of Tandem Breakers      | 10  |
| Number of Phases                       | 1 phase   |
| Voltage Rating                         | 120/240 V AC  |
| Wire Size                              | AWG 6...300 kcmil aluminium/copper                        |
| Ground Bar                             | Grounding bar included (not installed)                    |
| Busbar Material                        | Copper busbar   |
| Enclosure Material                     | Welded sheet steel  |
| Surface Finish                         | Baked enamel grey   |
| Box Number                             | 9Q  |
| Height                                 | 29.84 in (758 mm)   |
| Width                                  | 14.25 in (362 mm)   |

### Environment

|                                       |                                 |
|---------------------------------------|---------------------------------|
| Enclosure Rating                      | NEMA 1 for indoor               |
| Ambient Air Temperature for Operation | 23 °F (-5 °C)<br>104 °F (40 °C) |
| Product Certifications                | UL Listed                       |

### Ordering and shipping details

|                       |  |
|-----------------------|--|
| Category              | 10003 - QO PON 1PH LC,12-60 CKT, ML N1 |
| Discount Schedule     | DE3A                                   |
| GTIN                  | 00785901774341                         |
| Nbr. of units in pkg. | 1                                      |
| Package weight(Lbs)   | 1 lb(US) (0.45 kg)                     |
| Returnability         | Yes                                    |
| Country of origin     | US                                     |

## Packing Units

|                  |                      |
|------------------|----------------------|
| Package 1 Height | 4.50 in (11.430 cm)  |
| Package 1 width  | 14.70 in (37.338 cm) |
| Package 1 Length | 31.70 in (80.518 cm) |

## Offer Sustainability

|                            |   |
|----------------------------|---|
| REACH Regulation           | <a href="#">REACH Declaration</a>             |
| REACH free of SVHC         | Yes   |
| EU RoHS Directive          | Compliant <a href="#">EU RoHS Declaration</a> |
| Toxic heavy metal free     | Yes   |
| Mercury free               | Yes   |
| RoHS exemption information | <a href="#">Yes</a>                           |
| China RoHS Regulation      | <a href="#">China RoHS Declaration</a>        |