



Main

Product or component type	Section
---------------------------	---------

Complementary

Fixing mode	Plug-in
[Ue] rated operational voltage	600 V AC 50/60 Hz 277/480 V AC 50/60 Hz
Phase	3 phase
Busbar description	Ground
Fuse type	J
Breaking capacity code	D
Disconnecter device type	Associated circuit breaker 250 A 25 kA 240 V Associated circuit breaker 250 A 18 kA 480 V Associated circuit breaker 250 A 14 kA 600 V
Level or class	Class 5600
Wiring configuration	4-wire

Environment

Product certifications	UL CSA
------------------------	-----------

Ordering and shipping details

Category	20185-PJD C/B PLUGS
Discount Schedule	PE7
Package weight(Lbs)	32.00 lb(US) (14.515 kg)
Returnability	No

Offer Sustainability

Sustainable offer status	Green Premium product
California proposition 65	WARNING: This product can expose you to chemicals including: Nickel compounds, which is known to the State of California to cause cancer, and Bisphenol A (BPA), which is known to the State of California to cause birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov
EU RoHS Directive	Compliant EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration
Environmental Disclosure	Product Environmental Profile

Contractual warranty

Warranty

18 months
