

## Product data sheet

### Characteristics

# 8536SAG11V02S

NEMA Motor Starter, Type S, nonreversing, Size 00, 9A, 1 HP at 230 VAC, 5 kA SCCR, 1 phase, 2 pole, melting alloy, 120 VAC coil, NEMA 1



### Main

Product Type	Motor starter
Product Range	S
Starter Type	Non reversing

### Complementary

NEMA Size	00
Rated Current	9 A
Number of Poles	2P
Maximum Voltage Rating	600 V AC
Phase	1 phase
Type of Overload	Melting alloy 1
Horsepower Rating	0.33 HP 115 V AC 1 HP 230 V AC
SCCR	Circuit-breaker: 5 kA at 600 V AC Fuse: 5 kA at 600 V AC
Coil Voltage	110 V AC 50 Hz 120 V AC 60 Hz
Control Circuit Type	Separate control circuit
Control Units	No control units
Pilot Light	Without pilot light
Auxiliary Contacts	Without
Terminal Type	Screw clamp terminals
Height	10.00 in (254.00 mm)
Width	6.00 in (152.40 mm)
Depth	5.56 in (141.22 mm)

### Environment

Enclosure Type	NEMA 1 painted sheet steel
Certifications	UL Listed CSA NEMA

### Ordering and shipping details

Category	21191 - 8502,36 SA,SB(NOT S*R,T,W)
Discount Schedule	CP1
GTIN	00785901018711
Nbr. of units in pkg.	1
Package weight(Lbs)	7.12 lb(US) (3.23 kg)

Returnability	No
Country of origin	MX

### Packing Units

Package 1 Height	6.50 in (16.510 cm)
Package 1 width	6.50 in (16.510 cm)
Package 1 Length	10.50 in (26.670 cm)

### Offer Sustainability

California proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to <a href="http://www.P65Warnings.ca.gov">www.P65Warnings.ca.gov</a>
EU RoHS Directive	Not compliant
China RoHS Regulation	<a href="#">China RoHS Declaration</a>
PVC free	Yes

### Contractual warranty

Warranty	18 months
----------	-----------