

# Product data sheet

## Characteristics

# QOB120PL5393

Mini circuit breaker, QO, 20A, 1 pole, 120/240 VAC, 10 kA, Powerlink, bolt on mount, 60 in leads



### Main

Product	Circuit breaker
Range	QO
Current Rating	20 A
Voltage Rating	120/240 V AC
Mounting Type	Bolt-on
Number of Poles	1P
Circuit Breaker Type	Standard
Ratings	HACR rated
Electrical Connection	Box lugs

### Complementary

Interrupt Rating	10 KA 120/240 V AC 50/60 Hz 10 kA
Number of Panel Spaces	1
Provided Equipment	60 in (1524.00 mm) lead
Wire Size	AWG 12...AWG 2 aluminium AWG 14...AWG 2 copper
Tightening Torque	40.71 lbf.in (4.6 N.m)
Height	4.55 in (115.57 mm)
Width	0.75 in (19.05 mm)
Depth	2.91 in (73.91 mm)

### Environment

Certifications	UL Listed CSA
Ambient Rating	104 °F (40 °C)

### Ordering and shipping details

Category	09650 - POWERLINK QO(B)PL BREAKERS
Discount Schedule	DE8A
GTIN	00785901404750
Nbr. of units in pkg.	1
Package weight(Lbs)	0.6 lb(US) (0.27 kg)
Returnability	Yes
Country of origin	MX

### Packing Units

Package 1 Height	3.80 in (9.652 cm)
Package 1 width	1.30 in (3.302 cm)
Package 1 Length	5.40 in (13.716 cm)

## Offer Sustainability

California proposition 65	WARNING: Cancer and Reproductive Harm - <a href="http://www.P65Warnings.ca.gov">www.P65Warnings.ca.gov</a>
REACH Regulation	<a href="#">REACH Declaration</a>
REACH free of SVHC	Yes
EU RoHS Directive	Compliant <a href="#">EU RoHS Declaration</a>
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	<a href="#">Yes</a>
China RoHS Regulation	<a href="#">China RoHS Declaration</a>
Halogen content performance	Halogen free product

## Contractual warranty

Warranty	18 months
----------	-----------