

# Product data sheet

## Characteristics

# 3106340960

NEMA Motor Starter, Type S, replacement coil, 550/600 VAC 50/60 Hz, 2 or 3 pole, NEMA Size 2 starter and 8903SP lighting



### Main

Product or component type	Coil
Accessory / separate part destination	Class 8502 type SD contactor Class 8903 type SP lighting contactor

### Complementary

NEMA size	2
[Ue] rated operational voltage	600 V AC 60 Hz 550 V AC 50 Hz
Inrush power in VA	296 VA 311 VA
Average consumption	36 VA 37 VA
Height	2.61 in (66.2 mm)
Width	3.98 in (101.1 mm)
Depth	2.43 in (61.7 mm)

### Ordering and shipping details

Category	18061 - SPARE PARTS DISCOUNT CP1
Discount Schedule	CP1
GTIN	00785901049074
Nbr. of units in pkg.	1
Package weight(Lbs)	0.72 lb(US) (0.33 kg)
Returnability	Yes
Country of origin	MX

### Packing Units

Package 1 Height	2.80 in (7.112 cm)
Package 1 width	4.10 in (10.414 cm)
Package 1 Length	2.50 in (6.350 cm)

### Offer Sustainability

EU RoHS Directive	Not applicable, out of EU RoHS legal scope
-------------------	--

### Contractual warranty

Warranty	18 months
----------	-----------