



### Main

Range	TeSys
Device short name	VZ
Product or component type	Additional earthing block
Performance level	High performance
Contacts type and composition	Without
Product compatibility	V3 V4
Network type	DC AC
Network frequency	50/60 Hz

### Complementary

Mounting location	Left Right
[Ue] rated operational voltage	690 V AC 50/60 Hz
[Uimp] rated impulse withstand voltage	6 kV
[Ith] conventional free air thermal current	80 A
Connections - terminals	Screw clamp terminals
Height	3.27 in (83 mm)
Width	0.79 in (20 mm)
Depth	1.81 in (46 mm)
Net Weight	0.22 lb(US) (0.1 kg)

### Environment

Standards	IEC 60947-3
Product certifications	UL CSA GL UKCA
Protective treatment	TC
IP degree of protection	IP20 conforming to IEC 60529
Mechanical robustness	Vibrations 10...150 Hz 5 gn) IEC 60068-2-6 Shocks 11 ms 15 gn) IEC 60068-2-27
Ambient air temperature for operation	-4...122 °F (-20...50 °C)
Fire resistance	1760 °F (960 °C) IEC 60695-2-1

### Ordering and shipping details

Category	21730 - V VARIO SWITCH
Discount Schedule	CP1
GTIN	00785901613572
Nbr. of units in pkg.	1
Package weight(Lbs)	0.15 lb(US) (0.07 kg)
Returnability	Yes
Country of origin	CZ

## Packing Units

Unit Type of Package 1	PCE
Package 1 Height	1.46 in (3.7 cm)
Package 1 width	2.17 in (5.5 cm)
Package 1 Length	3.54 in (9 cm)
Unit Type of Package 2	S02
Number of Units in Package 2	69
Package 2 Weight	12.86 lb(US) (5.832 kg)
Package 2 Height	5.91 in (15 cm)
Package 2 width	11.81 in (30 cm)
Package 2 Length	15.75 in (40 cm)

## Offer Sustainability

Sustainable offer status	Green Premium product
REACH free of SVHC	Yes
EU RoHS Directive	Compliant <a href="#">EU RoHS Declaration</a>
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	<a href="#">Yes</a>
China RoHS Regulation	<a href="#">China RoHS Declaration</a>
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.

## Contractual warranty

Warranty	18 months
----------	-----------