



Main

| | |
|--|--|
| Product Type | Load Center value pack |
| Marketing Trade Name | Homeline |
| Load Center Type | Main breaker |
| Rated Current | 200 A |
| Number of Spaces | 40 |
| Maximum Number of Single Pole Circuits | 80 |
| Enclosure Rating | NEMA 1 for indoor |
| Cover Type | Combination flush/surface cover |
| Electrical Connection | Lugs |
| Provided Equipment | Circuit breaker 1) 2P 200 A 120/240 V AC main supply ready assembled Circuit breaker 3) 1P 20 A 120/240 V AC Circuit breaker 2) 2P 30 A 120/240 V AC |

Complementary

| | |
|-----------------------------------|------------------------------------|
| Max Short Circuit Current Rating | 22 kA |
| Maximum Number of Tandem Breakers | 40 |
| Number of Phases | 1 phase |
| Voltage Rating | 120/240 V AC |
| Wire Size | AWG 4...250 kcmil aluminium/copper |
| Ground Bar | Grounding bar (ordered separately) |
| Wiring Configuration | 3-wire |
| Busbar Material | Tin plated aluminium busbar |
| Enclosure Material | Welded sheet steel |
| Surface Finish | Baked enamel grey |
| Box Number | 12 |
| Height | 39.37 in (1000 mm) |
| Depth | 3.74 in (95 mm) |
| Width | 14.25 in (362 mm) |

Environment

| | |
|---------------------------------------|---------------------------------|
| Ambient Air Temperature for Operation | 23 °F (-5 °C) 104 °F (40 °C) |
| Product Certifications | UL listed file E-6294 |

Ordering and shipping details

| | |
|-----------------------|--------------------------------|
| Category | 00185 - MISC. HOM LOAD CENTERS |
| Discount Schedule | DE3C |
| GTIN | 00785901977513 |
| Nbr. of units in pkg. | 1 |
| Package weight(Lbs) | 39.7 lb(US) (18.01 kg) |
| Returnability | Yes |
| Country of origin | US |

Packing Units

| | |
|------------------------------|----------------------------|
| Unit Type of Package 1 | PCE |
| Package 1 Height | 5.71 in (14.5 cm) |
| Package 1 width | 16.30 in (41.4 cm) |
| Package 1 Length | 42.20 in (107.2 cm) |
| Unit Type of Package 2 | PAL |
| Number of Units in Package 2 | 18 |
| Package 2 Weight | 670.00 lb(US) (303.907 kg) |
| Package 2 Height | 40.00 in (101.6 cm) |
| Package 2 width | 40.00 in (101.6 cm) |
| Package 2 Length | 48.00 in (121.92 cm) |

Offer Sustainability

| | |
|----------------------------|---|
| Sustainable offer status | Green Premium product |
| California proposition 65 | WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov |
| REACH Regulation | REACH Declaration |
| REACH free of SVHC | Yes |
| EU RoHS Directive | Compliant EU RoHS Declaration |
| Toxic heavy metal free | Yes |
| Mercury free | Yes |
| RoHS exemption information | Yes |
| China RoHS Regulation | China RoHS Declaration |
| Environmental Disclosure | Product Environmental Profile |