

Protect It! 3-Outlet Travel-Size Surge Protector, 18-in. (45.72 cm) Cord, 1050 Joules, 2-USB Charging Ports

MODEL NUMBER: TRAVELER3USB



Highlights

- 3 AC power outlets
- 1050 Joule rating
- Concealable 18-inch Power Cord
- 2 USB Charging Ports - 2.1 amp total (5 VDC) for fast charging of cell phones, MP3 players, smartphones, tablets and more

Package Includes

- TRAVELER3USB Surge Suppressor
- Users Manual

Features

- 1050 joules of AC surge suppression shields equipment from the strongest surges and line noise
- 3 AC outlets with room for 1 transformer plug without blocking outlets
- 2 USB Charging Ports with 2.1 amps total is great for fast charging of cell phones, MP3 player, tablets, laptops and more.
- Portable housing with 18-in. concealable cord allow for ease of mobility and travel in briefcases
- "Protected" Diagnostic LED confirms outlet surge suppression status
- \$25,000 Ultimate Lifetime Insurance (U.S., Canada, and Puerto Rico only)
- Automatic shutoff permanently cuts power to outlets if protection circuit is incapacitated, preventing equipment damage and indicating replacement is required

Specifications

OVERVIEW	
UPC Code	037332149626
Product Type	Surge Protector
Charging Form Factor	Strip
Device Compatibility	Phone; Tablet; Amazon Kindle
INPUT	
Nominal Input Voltage(s) Supported	120V AC



Recommended Electrical Service	120V (110-125V)
Voltage Compatibility (VAC)	120
Maximum Surge Amps	36000
Input Plug Type	NEMA 5-15P
Input Cord Length (ft.)	1.5
Right-Angle Plug	Yes
Input Cord Length (m)	0.46
Integrated Cord Clip	No
OUTPUT	
Output Watt Capacity (Watts)	1800
Frequency Compatibility	60 Hz
Output (Watts)	1800
Output Receptacles	(3) 5-15R
Transformer Accommodation	(2) Yes
Output Amp Capacity	15
Right-Angle Outlets	No
USER INTERFACE, ALERTS & CONTROLS	
Diagnostic LED(s)	Yes
Diagnostic LED Details	Built-in LED confirm suppressor "protection present" (green) status
SURGE / NOISE SUPPRESSION	
AC Suppression Joule Rating	1050
Protection Modes	Includes Line to Neutral (L-N), Neutral to Ground (N-G) and Line to Ground (L-G) line surge suppression
Clamping Voltage (RMS)	400
Automatic Shut-Off	Yes
CHARGING	
Charging Ports / Amps	(2) 2.1A
Number of Charging Ports	2
Charging Method	USB
Charging Port Type	USB A (FEMALE)
DATALINE SURGE SUPPRESSION	
Telephone/DSL Protection	No
Cable (Coax) Protection	No



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

Network (Ethernet) Protection	No
PHYSICAL	
Color	Black
Antimicrobial Coating	No
Color (AC Line Cord)	Black
Integrated Keyhole Mounting Slots	No
Material of Construction	Plastic
Receptacle Color	Black
Shipping Dimensions (hwd / cm)	19.56 x 6.35 x 8.64
Shipping Dimensions (hwd / in.)	7.70 x 2.50 x 3.40
Shipping Weight (kg)	0.32
Shipping Weight (lbs.)	0.70
Unit Dimensions (hwd / cm)	14.48 x 7.52 x 3.56
Unit Dimensions (hwd / in.)	5.70 x 2.96 x 1.40
Unit Weight (kg)	0.28
Unit Weight (lbs.)	.62
CONNECTIONS	
Ports	2
SPECIAL FEATURES	
Rotatable Outlets	No
STANDARDS & COMPLIANCE	
Canada	cUL
UL1449 3rd Edition (AC Suppression)	UL1449
WARRANTY	
Product Warranty Period (Worldwide)	Lifetime limited warranty
Connected Equipment Insurance (U.S., Canada & Puerto Rico)	\$25,000 Ultimate Lifetime Insurance

© 2021 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <https://www.tripplite.com/products/product-certification-agencies>