



NOT for Patient-Care Rooms - UL1363 Hospital-Grade Surge Protector with 6 Hospital-Grade Outlets, 10 ft. (3.05 m) Cord, 1050 Joules

MODEL NUMBER: SPS610HGRA











Need to use a surge suppressor behind a desk or in a confined spot? The SPS610HGRA provides surge suppression with the convenience of a space-saving, right-angle hospital-grade plug for placing the units in confined areas and keyhole mounting tabs and flanges for easy installation.

Features

- 1050-joule AC surge suppression rating
- · Rugged all-metal housing withstands years of use without loss of ground path continuity
- 6 NEMA5-15R Hospital-Grade AC outlets
- 10-ft. AC cord with integrated, molded right angle Hospital-Grade NEMA 5-15PHG plug
- Keyhole mounting tabs and flanges
- · Switch safety cover prevents accidental shutoff
- 15A electrical capacity with built-in resettable circuit breaker
- 120 volt, 50/60Hz electrical compatibility
- Certified by UL (USA) and cUL (Canada)
- UL1449 3rd Edition listed
- Automatic shutoff permanently cuts power to outlets if protection circuit is incapacitated, preventing equipment damage and indicating replacement is required

Specifications

Highlights

- 6 hospital-grade outlets
- 1050 joule rating
- 10-ft. cord with molded rightangle hospital-grade plug
- · All metal housing

Package Includes

- SPS610HGRA Surge
 Suppressor
- Instruction manual with warranty information



OVERVIEW		
UPC Code	037332167071	
INPUT		
Nominal Input Voltage(s) Supported	120V AC	
Recommended Electrical Service	120V (110-125V)	
Voltage Compatibility (VAC)	120	
Maximum Surge Amps	19500	
Input Plug Type	NEMA 5-15P-HG	
Input Cord Length (ft.)	10	
Right-Angle Plug	Yes	
Input Cord Length (m)	3.05	
Integrated Cord Clip	No	
OUTPUT		
Frequency Compatibility	50 / 60 Hz	
Output (Watts)	1800	
Output Receptacles	(6) 5-15R-HG	
Circuit Breaker (amps)	15	
Transformer Accommodation	(2) Yes	
Right-Angle Outlets	No	
USER INTERFACE, ALERTS & CON	TROLS	
Diagnostic LED(s)	Yes	
Diagnostic LED Details	LINE POWER PRESENT (green)	
Locking Switch Cover	Locking switch cover	
SURGE / NOISE SUPPRESSION		
AC Suppression Joule Rating	1050	
AC Suppression Response Time	< 1 ns	
Protection Modes	Includes full normal mode surge suppression	
Clamping Voltage (RMS)	140	
Automatic Shut-Off	Yes	
DATALINE SURGE SUPPRESSION		
Telephone/DSL Protection	No	





Cable (Coax) Protection	No	
Network (Ethernet) Protection	No	
PHYSICAL		
Color	White	
Antimicrobial Coating	No	
Color (AC Line Cord)	Light Gray	
Integrated Keyhole Mounting Slots	Yes	
Material of Construction	Metal	
Receptacle Color	White	
Shipping Dimensions (hwd / cm)	5.59 x 38.10 x 15.24	
Shipping Dimensions (hwd / in.)	2.20 x 15.00 x 6.00	
Shipping Weight (kg)	1.18	
Shipping Weight (lbs.)	2.60	
Unit Dimensions (hwd / cm)	3.81 x 34.9 x 6.35	
Unit Dimensions (hwd / in.)	1.5 x 13.75 x 2.5	
Unit Weight (kg)	1.45	
Unit Weight (lbs.)	3.20	
SPECIAL FEATURES		
Rotatable Outlets	No	
STANDARDS & COMPLIANCE		
Canada	cUL (Series Number: AGIB12015SL)	
UL1449 3rd Edition (AC Suppression)	UL1449 3rd Edition (Series Number: AGIB12015SL)	
UL1363 (Power Tap)	UL1363 (Series Number: AGIB12015SL)	
WARRANTY		
Product Warranty Period (Worldwide)	Lifetime limited warranty	

© 2021 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: https://www.tripplite.com/products/product-certification-agencies