

# Product data sheet

## Characteristics

# 8911DPSG53V02

Starter, Definite Purpose, nonreversing, 50A, 3 pole, 3 phase, 120 VAC coil, melting alloy overload, NEMA 1, +options



### Main

Product	Definite Purpose Starter
Ampere Rating	50 A
Horsepower Rating	3 Hp 115 V AC, 1 phase 10 Hp 230 V AC, 1 phase 15 Hp 230 V AC, 3 phase 30 Hp 460 V AC, 3 phase 30 hp 575 V AC, 3 phase
Maximum Voltage Rating	600 V AC
Control Circuit Voltage	110 V AC 50 Hz 120 V AC 60 Hz
Phase	3 phase

### Complementary

Enclosure Material	Painted sheet steel
Enclosure Rating	NEMA 1
Locked Rotor Amperes	300 A 230 V AC 250 A 460 V AC 200 A 575 V AC
Number of Poles	3P
Range	DPS
Overload Type	Melting alloy
Number of Thermal Units	3

### Ordering and shipping details

Category	21381 - 8911 DP
Discount Schedule	CP1
GTIN	00785901024941
Nbr. of units in pkg.	1
Package weight(Lbs)	1 lb(US) (0.45 kg)
Returnability	No
Country of origin	CN

### Packing Units

Package 1 Height	7.30 in (18.542 cm)
Package 1 width	8.50 in (21.590 cm)
Package 1 Length	13.50 in (34.290 cm)

### Offer Sustainability

EU RoHS Directive	Compliant <a href="#">EU RoHS Declaration</a>
Mercury free	Yes
RoHS exemption information	<a href="#">Yes</a>
China RoHS Regulation	<a href="#">China RoHS Declaration</a>

### Contractual warranty

Warranty	18 months
----------	-----------