

SC8L125S

Meter mains, Homeline, combination service entrance, ringed socket, 125A, surface mount, maximum 8 spaces, no bypass



Main

Product or component type	Meter Mains
Range of product	Homeline

Complementary

Line Rated Current	125 A
Short-circuit current	10 kA
Network number of phases	1
Meter socket type	Ringed
Mounting	Surface
Number of spaces	8
Number of circuits	0
Number of Tandem Breakers	0
Hub type	A
Electrical connection	Lugs line side Lugs service ground
Wire Size	AWG 6...AWG 2/0 aluminium/copper)line side AWG 6...AWG 2/0 aluminium/copper)service ground
Disconnect	Service disconnect (ordered separately)
Main Breaker Rating	125 A
Service feed location	OH UG
Bypass type	No bypass
Height	26.50 in (673.10 mm)
Width	14.77 in (375.16 mm)
Depth	5.20 in (132.08 mm)

Environment

Product certifications	UL E-6294
------------------------	-----------

Ordering and shipping details

Category	00148 - HOMELINE CSED DEVICES
Discount Schedule	DE3A
GTIN	00785901308805
Nbr. of units in pkg.	1
Package weight(Lbs)	29.31 lb(US) (13.29 kg)
Returnability	Yes
Country of origin	MX

Packing Units

Package 1 Height	6.00 in (15.240 cm)
Package 1 width	15.30 in (38.862 cm)
Package 1 Length	26.80 in (68.072 cm)

Offer Sustainability

California proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov
REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Compliant EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration

Contractual warranty

Warranty	18 months
----------	-----------