



Main

Circuit Breaker Type	QBL QDL QGL QJL
Product Destination	Circuit breaker QB/QD/QJ/QL 3P Circuit breaker QB/QD/QJ/QL 2P

Complementary

Enclosure Material	Steel
Width	9.88 in (251 mm)
Height	26.26 in (667 mm)
Depth	4.76 in (121 mm)
Rated Current	100...225 A
Device Mounting	Surface
Poles Description	2P 3P
Tightening Torque	247.82 lbf.in (28 N.m) (AWG 4...300 kcmil)

Environment

Product Certifications	CSA UL
------------------------	-----------

Environmental

NEMA Degree of Protection	NEMA 1
NEMA Degree of Protection	NEMA 1

Ordering and shipping details

Category	00023 - QO,Q2L 3P ENCL & BREAKERS
Discount Schedule	DE2
GTIN	00785901993698
Nbr. of units in pkg.	1
Package weight(Lbs)	17.9 lb(US) (8.12 kg)
Returnability	Yes
Country of origin	MX

Packing Units

Package 1 Height	5.30 in (13.462 cm)
Package 1 width	10.20 in (25.908 cm)
Package 1 Length	26.90 in (68.326 cm)

Offer Sustainability

Sustainable offer status	Green Premium product
California proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov
EU RoHS Directive	Compliant EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration
Environmental Disclosure	Product Environmental Profile
PVC free	Yes
Halogen content performance	Halogen free plastic parts product

Contractual warranty

Warranty	18 months
----------	-----------